



DryLin® N miniature guiding system

Load up to 1000N

NK80
NW80

Small but
effective

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:



Slide body: Plastic

Rails: Anodised aluminium

- Symmetrical hole pattern, C5=C6

Options

- Rail length up to 3960mm max.



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-80-1000	1 Rail (1000mm) + 1 slide	1240	✓	106,74 €
NW02-80	1 slide only	100	✓	14,12 €

*Depending on availability - Dimensions in mm


Our other products



PMC48_M8
Anti-vibration machine mount, Oval base plate



SSB
Stainless steel bevel gear, 1:1




RPP
Connecting plate for RPP type timing belts, RRP5




SH2
Parallel axis helical gear, Machined plastic (delrin)



SCH
Horizontal hook toggle clamp, Horizontal Hook clamp - stainless steel



TC1rp
Automatic chain tensioner, With 180° guide



GPLss
Brush, stainless steel



PRF_CLIP_45
Cable clip for aluminium profile, For cable chute



HS
Hexagonal spacer, Stainless steel 303



AHEx
Hexagonal shaft, Hexagonal shaft



CHTRP
Single and dual output gearboxes, Up



DILC
Indexing plunger with cam, with cam

Complementary products



NSKB
Drylin® Rail end cap, Rail end cap