

Self tapping inserts- coarse thread

INS100

For soft materials


- Self tapping insert with coarse external thread
- No collar
- Deforms on installation, no special tools required
- Hexagonal drive socket simplifies installation
- Chromed steel

Applications

- For use in rubber, soft plastic or soft wood

Info.

- Sold by the packet



DISCOUNTS

Qty	1+	10+	20+	30+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	L	Ød	SW	Recommended Ø drill		Packet qty	Weight (g)	Stock*	Price each by packet
					min	max				
INS100-M4/B	8,0	8	M4	4	6,6	6,9	20	1,4	✓	10,27 €
INS100-M5/B	10,0	10	M5	5	8,4	8,9	20	2,5	✓	13,06 €
INS100-M6/B	12,0	12	M6	6	10,0	10,4	20	4,8	✓	16,25 €
INS100-M8/B	14,0	15	M8	8	12,0	12,4	20	7,3	✓	27,27 €
INS100-M10/B	18,5	20	M10	10	16,2	16,7	15	19,2	✓	42,60 €
INS100-M12/B	22,0	30	M12	12	19,5	20,0	10	38,0	-	127,30 €

*Depending on availability - Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15€/min + prix appel

Our other products



HLUMss

Revolving handle for handwheel, Stainless steel 316



PRF_P

Anchor foot for 45x45 profile, Anchor foot



H0

Crossed helical gear crossed axis at 90°, Steel 20NCD2



WINGbr

Wing screw, hand tightened DIN316, Brass DIN 316



ACLAPA

Magnetic stop for aluminium profile, Magnetic stop



T25-6ECO

T type timing pulley, Economy range - T2.5 aluminium



BEK

Bearing housing for miniature ballscrew, Bearing housing



AZY

Cylindrical elastomeric mount, Steel



HSSss

Stainless steel shoulder screw



RFVbr

Stainless steel reaction arm,



RT61

Self-centering locking Assembly,



RHTplss

High Temperature Castor, up to 200kg

Complementary products



INS150

Self tapping insert with collar-coarse thread, With collar-coarse t...



INS

Self tapping steel insert, Steel



BOX-INS-W

Box set of self tapping inserts, Boxed set - For wood



INSTool

Insertion tool for self tapping inserts, Insertion tool