

Self tapping insert with collar-coarse thread

For soft materials

INS150

- Self tapping insert with coarse external thread
- With collar
- Deforms on installation, no special tools required
- Hexagonal drive socket simplifies installation
- Chromed steel

Applications



- For use in rubber, soft plastic or soft wood

Advantage

- Collar prevents insert being inserted too far

Info.

- Sold by the packet



DISCOUNTS

Qty	1+	10+	20+	30+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	L	Ød	SW	Recommended Ø drill		Packet qty	Weight (g)	Stock*	Price each by packet
					min	max				
INS150-M4/B	8,0	8	M4	4	6,6	6,9	20	1,4	✓	29,28 €
INS150-M5/B	10,0	12	M5	5	8,4	8,9	20	2,8	✓	36,42 €
INS150-M6/B	12,0	15	M6	6	10,0	10,4	20	6,0	✓	42,90 €
INS150-M8/B	14,0	18	M8	8	12,0	12,4	20	8,7	✓	71,53 €
INS150-M10/B	18,5	25	M10	10	16,2	16,7	15	24,2	✓	83,54 €
INS150-M12/B	22,0	25	M12	12	19,5	20,0	10	34,5	-	100,78 €

*Depending on availability - Dimensions in mm

Our other products



NSP

Right angled support clamp, Right angled support clamp



MSP38

Masterplate® glueable insert Ø38, Cylindrical Ø38 with tapped ins...



BPL

Ball transfer unit light duty, Light



PRF JL4

Lip seal for panel, Door seal - Ø 4mm



HTD5M_25

HTD Heavy duty timing pulley, HTD5 Aluminium



VT

Vari-Tork® slip friction clutch, 0.53 to 1.32 Nm



PRF_ROUL

Castor for aluminium profile, No brake



CHAC4040SS

Square hinge with riveted pin, drilled, Square with riveted pin, dri...



RPCtcss

Swivel castor with central hole, Stainless



PTAF100-PAMF100

Articulated fixable foot with pressed



BABFCFO

Ball pin socket, Mounting collar with a



CABtool

Fitting cable tools, Cutting tools

Complementary products



INS100

Self tapping inserts-coarse thread, Coarse thread



BOX-INS-W

Box set of self tapping inserts, Boxed set - For wood



INSTool

Insertion tool for self tapping inserts, Insertion tool



CHC

Socket headed screw, Steel class 12.19