

Self tapping insert with collar-coarse thread

For soft materials

INS150

- Self tapping insert with coarse external thread
- With collar
- Deforms on installation, no special tools required
- Hexagonal drive socket simplifies installation
- Chromed steel

Applications



- For use in rubber, soft plastic or soft wood

Advantage

- Collar prevents insert being inserted too far

Info.

- Sold by the packet



DISCOUNTS

Qty	1+	10+	20+	30+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	L	Ød	SW	Recommended Ø drill		Packet qty	Weight (g)	Stock*	Price each by packet
					min	max				
INS150-M4/B	8,0	8	M4	4	6,6	6,9	20	1,4	✓	29,28 €
INS150-M5/B	10,0	12	M5	5	8,4	8,9	20	2,8	✓	36,42 €
INS150-M6/B	12,0	15	M6	6	10,0	10,4	20	6,0	✓	42,90 €
INS150-M8/B	14,0	18	M8	8	12,0	12,4	20	8,7	✓	71,53 €
INS150-M10/B	18,5	25	M10	10	16,2	16,7	15	24,2	✓	83,54 €
INS150-M12/B	22,0	25	M12	12	19,5	20,0	10	34,5	-	100,78 €

*Depending on availability - Dimensions in mm

Our other products



UGAC_UGET
Actuator guide kit,
Coupling for threaded
cylinder end



PSG08S
Spur gear - precision
range, Stainless steel
316




T2,5-BAR
T type tooth bar
stock, T2.5



PTCR
Adjustable furniture
foot, square tube



CHA_GC_9SS
Stainless steel garnet
hinge, To be welded



M1
Worm and wheel set,
Machined plastic
(delrin)



TAC_SS
Stainless steel rigging
screw (hook/eye),
Stainless steel



CAP880
Side flexing slim slat
top chain acetal,
Narrow range 880




HRV
V-rail guidance
Simple Select®



PITAss
Locking bolt, with T
handle



DOMI80
Connecting kits, XZ
linking kit



M2
Worm and wheel set,
Bronze

Complementary products



INS100
Self tapping inserts-
coarse thread, Coarse
thread



BOX-INS-W
Box set of self tapping
inserts, Boxed set -
For wood



INSTool
Insertion tool for self
tapping inserts,
Insertion tool



CHC
Socket headed screw,
Steel class 12.19