


# Insertion tool for self tapping inserts

Assembly tool

INSTOOL

- Insertion tool for self tapping inserts
- Hexagonal shaft and rotating hexagonal end



Example of a typical application

## DISCOUNTS

Qty	1+	10+	20+	30+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	Ød	SW	Stock*	Price each 1 to 9
INS300-TOOL-M3	M3	10	✓	89,30 €
INS300-TOOL-M4	M4	10	✓	89,30 €
INS300-TOOL-M5	M5	17	✓	101,20 €
INS300-TOOL-M6	M6	17	✓	101,20 €
INS300-TOOL-M8	M8	17	✓	116,11 €
INS300-TOOL-M10	M10	19	✓	122,06 €
INS300-TOOL-M12	M12	19	✓	157,79 €

\*Depending on availability - Dimensions in mm

## Our other products



BCA

Steel splined collar,  
Steel



PP60

Worm and wheel gear  
reducer, from 17.80  
to 34 Nm



LC

Friction clutch, 190 to  
1800 Nm



CHT

Asynchronous AC  
Motor 1.1 to 1.85kW,  
1.1 to 1.85kW



MHWC

Double-disc flexible  
coupling, Double disk



PRF3232

Standard aluminium  
profile, 32 x 32 mm



H3

Crossed helical gear  
crossed axis at 90°,  
Machined plastic  
(delrin)



SH1

Parallel axis helical  
gear, Steel 20NCD2



PCF2

Conical flexible  
mount, Oval base  
plate



OP2

Mechanical digital  
position indicator, 3  
numbers



CCL

Standard wire  
thimble, Steel



LSAG

Sleeve for splined ball  
shaft, Chariot - from  
514 N to 15386 N

## Complementary products



INS

Self tapping steel  
insert, Steel



INS\_BR

Self tapping brass  
insert, Brass



INS\_SS

Self tapping stainless  
steel insert, Stainless  
steel



INS100

Self tapping inserts-  
coarse thread, Coarse  
thread