


Insertion tool for self tapping inserts

Assembly tool

INSTOOL

- Insertion tool for self tapping inserts
- Hexagonal shaft and rotating hexagonal end



Example of a typical application

DISCOUNTS

Qty	1+	10+	20+	30+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	Ød	SW	Stock*	Price each 1 to 9
INS300-TOOL-M3	M3	10	✓	89,30 €
INS300-TOOL-M4	M4	10	✓	89,30 €
INS300-TOOL-M5	M5	17	✓	101,20 €
INS300-TOOL-M6	M6	17	✓	101,20 €
INS300-TOOL-M8	M8	17	✓	116,11 €
INS300-TOOL-M10	M10	19	✓	122,06 €
INS300-TOOL-M12	M12	19	✓	157,79 €

*Depending on availability - Dimensions in mm

Fax: 0 825 88 6000 > Service 0,15€/mln + prix appel

cial2@hpceurope.com

WEB
04/2020

HPC

Our other products



PRFRTR
Cross connector for aluminium profile, Cross connector



GDR880
Straight track for slat top chain, Ranges 880 and 881



UGH50
H Type Guide units, For Ø50 actuators



SSDB
Stainless steel bevel gear, 2:1



H02
Single needle roller universal joint, Heavy duty



CHM40
Worm and wheel gear reducer, up to 57 Nm



HRV
V- rail guidance Simple Select® system, Rail with carriage




GBS
Nut for ballscrew, Flanged ballscrew nut



CHTRP
Single and dual output gearboxes, Up to 87,3Nm



PRF_PSA
Shaft support for aluminium profile, Linear guide shaft



MET
Cylindrical sintered bronze bush, Self-lubricating sintered



GP
Spring loaded toggle latch, Standard (GP22-GP23)

Complementary products



INS
Self tapping steel insert, Steel



INS_BR
Self tapping brass insert, Brass



INS_SS
Self tapping stainless steel insert, Stainless steel



INS100
Self tapping inserts-coarse thread, Coarse thread