

Pull handle

PCA



Thermoplastic

Gripping handle for both pushing and pulling

- Rear mounting
- Working T° -30°C to +130°C
- Materials:
 - Thermoplastic PA6 glass fiber reinforced
 - Brass inserts with tapped blind hole

Advantages

- Very strong
- 110mm and 120mm centres correspond to German standards
- No product retention



DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	B	A	E	F	C	H	ØD	Weight (g)	Stock*	Price each 1 à 5
PCA93-M5	93,5±0,5	111	23	36	29	9	M5	41	-	5,31 €
PCA93-M6	93,5±0,5	111	23	36	29	9	M6	42	-	5,31 €
PCA105-M5	105±0,5	121	26	37	29	9	M5	46	-	5,67 €
PCA105-M6	105±0,5	121	26	37	29	9	M6	48	-	5,67 €
PCA110-M5	110±0,5	133	26	40	32	9	M5	58	-	6,18 €
PCA110-M6	110±0,5	133	26	40	32	9	M6	60	-	6,18 €
PCA117-M5	117±1	133	26	40	32	9	M5	57	-	6,39 €
PCA117-M6	117±1	133	26	40	32	9	M6	59	-	6,39 €
PCA117-M8	117±1	133	26	40	32	9	M8	61	-	6,39 €
PCA120-M8	120±1	137	26	40	32,5	9	M8	58	-	6,48 €
PCA132-M8	132±1	150	26	45	37	9	M8	68	-	7,38 €
PCA150-M8	150±1	169	27	45	37	9	M8	76	-	8,25 €
PCA179-M8	179±1	200	28	51	42	9	M8	101	-	9,42 €
PCA179-M10	179±1	200	28	51	42	13	M10	101	-	9,45 €

*Depending on availability - Dimensions in mm

Our other products



GLT3E-50

Telescopic drawer,



SCH

Horizontal hook
toggle clamp,
Horizontal Hook
clamp - stainless steel



DOMI120

Accessories, Clamping
lever




BLH70

Right angled gearbox,
from 26 to 128 Nm



BIMSS

Indexing plunger mini,
miniature - Stainless
steel



BOX-TOR-TOOL

Box set of tool for
Nitrile O-rings,
Extraction tools



HTD5M_25

HTD Heavy duty
timing pulley, HTD5
Steel



HBM

Adjustment bushing
for half-rail guide,
Adjustment bushing



UTKswc

Utilitrak® 3 wheels
carriage, Series V



ACLLPP

Latch for aluminium
profile, Spring



gt64

Rotating bent lever,
Common applications



CHAR7530

Spring hinge, welded

Complementary products




PO

Pull handle - Multi-
sector, Smooth hole




PO

Pull handle - Multi-
sector, Tapped
recessed insert



PO

Pull handle - Multi-
sector, Smooth hole



PO

Pull handle - Multi-
sector, Smooth hole