



# Clamp lever

With male thread

PCLAT  
PCLATss

- Clamp lever with male thread and reduced tip according to DIN 78

- Materials:

Insert: steel (class 5.8) or stainless steel (303)

Handle: glass fibre reinforced polyamide plastic

Mechanism: splined diecast zinc

- Finish: Blackened steel, fine grained surface

- Matte surface with fine grains

- Colour: black

- Working temp.: -50°C to +130°C

## Uses


- The lever is normally in a locked position

- Raise the handle to release the lever and turn to required position

- When handle is released, lever will automatically lock in new position

## Info.

- H4 = clearance height required for handle



## DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number		Threaded bolt X	H1	L			ØD	ØD1	H
Steel	Stainless			Steel	StS				
PCLA01T5	PCLA01T5SS	M5	4.0	50	25	10.0	13.0	24.5	
PCLA01T6	PCLA01T6SS	M6	4.0	50	50	10.0	13.0	24.5	
PCLA02T8	PCLA02T8SS	M8	6.5	60	60	13.5	18.0	28.5	
PCLA02T10	PCLA02T10SS	M10	6.5	60	60	13.5	18.0	28.5	
PCLA03T10	PCLA03T10SS	M10	10.0	60	60	16.0	21.5	37.0	
PCLA04T10	-	M10	10.0	90	-	19.0	25.5	43.0	
PCLA04T12	PCLA04T12SS	M12	10.0	90	60	19.0	25.5	43.0	
PCLA05T12	-	M12	12.0	90	-	23.0	30.0	49.0	
PCLA05T16	PCLA05T16SS	M16	12.0	90	60	23.0	30.0	49.0	

Part number		Stock*							Price each 1 to 5		
Steel	Stainless	A	H2	H3	H4	A1	B	Steel	StS	Stainless	
PCLA01T5	PCLA01T5SS	40	15.0	30.0	33.5	47.0	7.5	✓	✓	9.83 €	13.52 €
PCLA01T6	PCLA01T6SS	40	15.0	30.0	33.5	47.0	7.5	✓	✓	9.83 €	14.53 €
PCLA02T8	PCLA02T8SS	65	17.5	41.5	45.5	75.0	9.5	✓	✓	11.46 €	17.36 €
PCLA02T10	PCLA02T10SS	65	17.5	41.5	45.5	75.0	9.5	✓	✓	11.46 €	17.36 €
PCLA03T10	PCLA03T10SS	80	24.0	53.5	58.0	91.5	11.0	✓	✓	14.14 €	21.57 €
PCLA04T10	-	95	26.0	61.0	66.0	109.0	13.0	✓	-	18.72 €	-
PCLA04T12	PCLA04T12SS	95	26.0	61.0	66.0	109.0	13.0	✓	✓	18.72 €	31.50 €
PCLA05T12	-	110	33.0	72.0	77.0	126.0	15.5	-	-	23.18 €	-
PCLA05T16	PCLA05T16SS	110	33.0	72.0	77.0	126.0	15.5	-	-	23.18 €	37.27 €

\*Depending on availability - Dimensions in mm

## Our other products



PRF\_FIX\_UNI  
Universal fastener for aluminium profile, Universal



GGB  
Female wing knob, Fully threaded



BTCW  
Cap for square tube to be welded, To be welded



GCH  
Linear ball slide Eco Range, economy range



CHCSS  
Socket headed screw, Stainless steel - A2



BOX-TOR-INCH  
Box set of Nitrile O-rings in inch NBR90Sh A, For fasteners and fittings



INSTool  
Insertion tool for self tapping inserts, Insertion tool



CNA-CNG  
Right angled mounting plate, Right angled mounting plate for clevis



RAG  
Roller guide,



SLH  
Horizontal toggle clamp, Horizontal Lever Clamp - steel



VAB  
Flanged nut for ball screw, For VAB ballscrew



MSP38  
Masterplate® glueable insert Ø38, Cylindrical Ø38 with tapped inserts

## Complementary products



CLB\_T  
Die cast zinc clamping lever - male, Zamak



CLASS  
Stainless steel indexing handle - male, Stainless steel



PCLA\_M  
Technopolymer clamping lever - female, Plastic



CLB\_M  
Die cast zinc clamping lever - female, Zamak