

**- Element of manual blocking**

**- Materials**

Handle: Electrolytically stainless steel


Z6CN18.10M

Thrust washer: glass fibre reinforced

black plastic PA 6 GF 30

Hinge pin, threaded stud and washer:

polished stainless steel 303



### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request



Part number	Thread	$\text{ØD}$	$\text{ØD1}$	$\text{ØD2}$	B	B1	H	H1	A	A1	Clamping force	Manual force	Stroke	Price each 1 to 5
											F (kN)	N	S	
LAC-M5/SS	M5	18	9	21,5	15	14,5	22,0	70,4	79,2	4	120	1,2	✓	25,99 €
LAC-M6/SS	M6	18	9	21,5	15	14,5	22,0	70,4	79,2	4	120	1,2	✓	25,99 €
LAC-M8/SS	M8	27	11	33,2	24	18,0	28,5	96,0	108,0	8	350	1,5	✓	36,06 €

\*Depending on availability - Dimensions in mm

## Our other products



**PTR**  
Idler chain sprocket,  
For standard  
applications



**GGP**  
Male wing knob,  
Technopolymer with  
stainless steel spindle



**PRF\_SDD\_1820**  
Support for Ø18 or  
Ø20mm Prox  
detector, Ø18 and  
Ø20



**EHD12**  
Internal epicyclic  
servo reducers, from  
60 to 140 Nm



**CHA1056\_U4**  
Screw-in hinge,  
Section 40X40



**BCTH**  
Mushroom headed  
button Hygienic  
Usit®, With female  
thread and high ...



**MSP23**  
Masterplate®  
glueable insert Ø23,  
Cylindrical Ø23 with  
threaded s...



**AC156-157**  
Strike for toggle latch,  
25.5mm




**PSG15S**  
Spur gear - precision  
range, Stainless steel



**PDD**  
Actuating plunger,  
Non-rotating detector



**NPTF20**  
Fixed tube carrier,  
Fixed Ø10 to Ø14



**T0**  
Torsion spring,  
Stainless steel

## Complementary products



**LACT\_SS**  
Adjustable Stainless  
steel cam lever, Male