



With male thread

PCLAT
PCLATss

- Clamp lever with male thread and reduced tip according to DIN 78

- Materials:

- Insert: steel (class 5.8) or stainless steel (303)

- Handle: glass fibre reinforced polyamide plastic

- Mechanism: splined diecast zinc



- Finish: Blackened steel, fine grained surface

- Matte surface with fine grains

- Colour: black

- Working temp.: -50°C to +130°C

With male
thread



Uses

- The lever is normally in a locked position
- Raise the handle to release the lever and turn to required position
- When handle is released, lever will automatically lock in new position

Info.

- H4 = clearance height required for handle

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number			L							
Steel	Stainless	Threaded bolt X	H1	Steel	StS	ØD	ØD1	H		
PCLA01T5	PCLA01T5SS	M5	4,0	50	25	10,0	13,0	24,5		
PCLA01T6	PCLA01T6SS	M6	4,0	50	50	10,0	13,0	24,5		
PCLA02T8	PCLA02T8SS	M8	6,5	60	60	13,5	18,0	28,5		
PCLA02T10	PCLA02T10SS	M10	6,5	60	60	13,5	18,0	28,5		
PCLA03T10	PCLA03T10SS	M10	10,0	60	60	16,0	21,5	37,0		
PCLA04T10	-	M10	10,0	90	-	19,0	25,5	43,0		
PCLA04T12	PCLA04T12SS	M12	10,0	90	60	19,0	25,5	43,0		
PCLA05T12	-	M12	12,0	90	-	23,0	30,0	49,0		
PCLA05T16	PCLA05T16SS	M16	12,0	90	60	23,0	30,0	49,0		

Part number			Stock*								Price each 1 to 5	
Steel	Stainless	A	H2	H3	H4	A1	B	Steel	StS	Steel	Stainless	
PCLA01T5	PCLA01T5SS	40	15,0	30,0	33,5	47,0	7,5	✓	✓	9,83 €	13,52 €	
PCLA01T6	PCLA01T6SS	40	15,0	30,0	33,5	47,0	7,5	✓	✓	9,83 €	14,53 €	
PCLA02T8	PCLA02T8SS	65	17,5	41,5	45,5	75,0	9,5	✓	✓	11,46 €	17,36 €	
PCLA02T10	PCLA02T10SS	65	17,5	41,5	45,5	75,0	9,5	✓	✓	11,46 €	17,36 €	
PCLA03T10	PCLA03T10SS	80	24,0	53,5	58,0	91,5	11,0	✓	✓	14,14 €	21,57 €	
PCLA04T10	-	95	26,0	61,0	66,0	109,0	13,0	✓	-	18,72 €	-	
PCLA04T12	PCLA04T12SS	95	26,0	61,0	66,0	109,0	13,0	✓	✓	18,72 €	31,50 €	
PCLA05T12	-	110	33,0	72,0	77,0	126,0	15,5	-	-	23,18 €	-	
PCLA05T16	PCLA05T16SS	110	33,0	72,0	77,0	126,0	15,5	-	-	23,18 €	37,27 €	

*Depending on availability - Dimensions in mm

Our other products



SUPccss

Self-centering
clamping hub
stainless steel, With
lock nut



INS

Self tapping steel
insert, Steel



CHM63-MOT

Asynchronous AC
motorgearboxes 0.37
to 1.5kW, 0.37 to
1.5kW



SLBWSS

Indexing plunger,
weldable, Weldable -
Stainless steel



VDSQCB

Sliding lock
adjustment system,
Blocking wedge



DOMI120

Domino 120
adjustable slide, Slide
DOMILINE 120



ACLEPP

Right angled bracket
for aluminium profile,
4 holes



BH01

Single housed
bearing, Bearing fitted
with adhesive



BLHM60

Right angled gearbox,
double output shafts,
up to 70 Nm



GLP

Small 6 lobe threaded
handle - male,
Technopolymer -
Stainless steel



PSPE20

Conical flexible shaft
handle Ø20, Black
PVC



KBS_UU

Stainless steel closed
precision linear
bearing, Precision -
stainle...

Complementary products



CLB_T

Die cast zinc clamping
lever - male, Zamak



CLASS

Stainless steel
indexing handle -
male, Stainless steel



PCLA_M

Technopolymer
clamping lever -
female, Plastic



CLB_M

Die cast zinc clamping
lever - female, Zamak