

Mounting feet with integrated castors

Offset castor

PDR


- Combines the advantages of a static mounting foot and a castor
- Use a hexagonal spanner to release the castor
- Castor protrudes 12.5mm when released
- Only for use on surfaces that are smooth (crevices less than 5mm) and horizontal (max slope 3°)
- Max static load 2,500 kg per foot
- Max load 200 kg per foot if used in movable mode
- Materials:
 - Base - Polyamide
 - Sole - NBR rubber
 - Threaded shaft - Chromed steel

Typical application


- A vessel remains static whilst the product within is processed but once empty, can be moved for cleaning purposes.

Advantages

- Flexibility (1 item performs 2 functions)
- Less manoeuvring to move a structure
- Time saving



Retracting the castor



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	L	Load Castor fixed (static) (kg)	Load Castor free (dynamic) (kg)	Price each 1 to 5
With threaded shaft					
PDR100-16-50/RD	M16	50	2500	200	118,60 €
PDR100-16-100/RD	M16	100	2500	200	122,18 €
PDR100-20-75/RD	M20	75	2500	200	122,18 €
PDR100-20-125/RD	M20	125	2500	200	125,78 €
PDR100-24-75/RD	M24	75	2500	200	122,18 €
PDR100-24-125/RD	M24	125	2500	200	125,78 €
With 80x80mm mounting plate					
PDR100-80-80/RD	4x8.5mm holes		2500	200	122,18 €

Dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019


281

Our other products



NSP

Right angled support clamp, Right angled support clamp



RPPM

RPP type belt per metre, RPP8 Steel cored polyurethane



V3RA

3-spoked handwheel without handle, Polyamide



PGMSS

Stainless steel push/pull handle, Stainless steel



DGSA

Male rod ends, Steel / steel - Economy range



PGMT

Pull handle, Stainless steel



INS

Self tapping steel insert, Steel



BLHM30

Right angled gearbox, double output shafts, up to 4.4 Nm



LRR-53

Spring loaded latch, Spring return latch - steel



IBJ

180° ball and socket joints, Steel



ES

Bipod support base, Plastic



CLAT

Clamping lever Hygienic Usit® - male, Stainless steel

Complementary products



RIMtce

Locking castor, with central hole



RIMple

Locking castor, with mounting plate