

Mounting feet with integrated castors

Offset castor

PDR


- Combines the advantages of a static mounting foot and a castor
- Use a hexagonal spanner to release the castor
- Castor protrudes 12.5mm when released
- Only for use on surfaces that are smooth (crevices less than 5mm) and horizontal (max slope 3°)
- Max static load 2,500 kg per foot
- Max load 200 kg per foot if used in movable mode
- Materials:
 - Base - Polyamide
 - Sole - NBR rubber
 - Threaded shaft - Chromed steel

Typical application


- A vessel remains static whilst the product within is processed but once empty, can be moved for cleaning purposes.

Advantages

- Flexibility (1 item performs 2 functions)
- Less manoeuvring to move a structure
- Time saving



Retracting the castor



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	L	Load Castor fixed (static) (kg)	Load Castor free (dynamic) (kg)	Price each 1 to 5
With threaded shaft					
PDR100-16-50/RD	M16	50	2500	200	118,60 €
PDR100-16-100/RD	M16	100	2500	200	122,18 €
PDR100-20-75/RD	M20	75	2500	200	122,18 €
PDR100-20-125/RD	M20	125	2500	200	125,78 €
PDR100-24-75/RD	M24	75	2500	200	122,18 €
PDR100-24-125/RD	M24	125	2500	200	125,78 €
With 80x80mm mounting plate					
PDR100-80-80/RD	4x8.5mm holes		2500	200	122,18 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Our other products




SFE
Female rod ends,
Stainless steel / PTFE



APBC
Circular rod, Round
rod



HK
Manual locking clamp,
Manual locking clamp
LWH




VKM
Square steel nut,
Steel - 1 thread




CHAR7520
Spring hinge, screwed



VLBS
Folding lifting ring for
welding, Folding - for
welding



RPP8
RPP heavy duty
timing belt, RPP8



VP
Small 6 lobe threaded
handle - male,
Duroplast - Steel



BAN
Angular clamp,
Adjustable



H3
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



MFB_MHB
Moulded plastic bevel
gear (nylon), 1.5:1



NT63
Spur gear coaxial
gearbox, from 8 to 20
Nm - Inline

Complementary products



RIMtce
Locking castor, with
central hole



RIMple
Locking castor, with
mounting plate