

Mounting feet with integrated castors

Offset castor

PDR


- Combines the advantages of a static mounting foot and a castor
- Use a hexagonal spanner to release the castor
- Castor protrudes 12.5mm when released
- Only for use on surfaces that are smooth (crevices less than 5mm) and horizontal (max slope 3°)
- Max static load 2,500 kg per foot
- Max load 200 kg per foot if used in movable mode
- Materials:
 - Base - Polyamide
 - Sole - NBR rubber
 - Threaded shaft - Chromed steel

Typical application


- A vessel remains static whilst the product within is processed but once empty, can be moved for cleaning purposes.

Advantages

- Flexibility (1 item performs 2 functions)
- Less manoeuvring to move a structure
- Time saving



Retracting the castor



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	L	Load Castor fixed (static) (kg)	Load Castor free (dynamic) (kg)	Price each 1 to 5
With threaded shaft					
PDR100-16-50/RD	M16	50	2500	200	118,60 €
PDR100-16-100/RD	M16	100	2500	200	122,18 €
PDR100-20-75/RD	M20	75	2500	200	122,18 €
PDR100-20-125/RD	M20	125	2500	200	125,78 €
PDR100-24-75/RD	M24	75	2500	200	122,18 €
PDR100-24-125/RD	M24	125	2500	200	125,78 €
With 80x80mm mounting plate					
PDR100-80-80/RD	4x8.5mm holes		2500	200	122,18 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC


SUPPLEMENT 2019

281


Our other products



MHMEP
Arm with rotating handle, Prebored



PM4
Wormwheel, Machined plastic (delrin)



PF20NM
Worm and wheel gear reducer, up to 5 Nm



FF15
Offset spur gear reducer, from 2.20 to 10 Nm



GAC
Lock for latch clamp, Strike plate




BAP25
Plastic clamping collar, Ø25 - Ø40



P70
Worm and wheel gear reducer, up to 164 Nm




PRF JL2
Lip seal for panel, Door seal - Ø 2mm



SHTP
Drylin® Linear table, Economy range



PSG08S
Spur gear - precision range, Stainless steel




AC
Strike for toggle latch, 12mm



PRF CHA D
Hinge and joint, Lift-off hinge

Complementary products



RIMtce
Locking castor, with central hole



RIMple
Locking castor, with mounting plate