

# Mounting feet with integrated castors

## Offset castor

## PDR


- Combines the advantages of a static mounting foot and a castor
- Use a hexagonal spanner to release the castor
- Castor protrudes 12.5mm when released
- Only for use on surfaces that are smooth (crevices less than 5mm) and horizontal (max slope 3°)
- Max static load 2,500 kg per foot
- Max load 200 kg per foot if used in movable mode
- Materials:
  - Base - Polyamide
  - Sole - NBR rubber
  - Threaded shaft - Chromed steel

### Typical application


- A vessel remains static whilst the product within is processed but once empty, can be moved for cleaning purposes.

### Advantages

- Flexibility (1 item performs 2 functions)
- Less manoeuvring to move a structure
- Time saving



Retracting the castor



### DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	L	Load Castor fixed (static) (kg)	Load Castor free (dynamic) (kg)	Price each 1 to 5
<b>With threaded shaft</b>					
PDR100-16-50/RD	M16	50	2500	200	118,60 €
PDR100-16-100/RD	M16	100	2500	200	122,18 €
PDR100-20-75/RD	M20	75	2500	200	122,18 €
PDR100-20-125/RD	M20	125	2500	200	125,78 €
PDR100-24-75/RD	M24	75	2500	200	122,18 €
PDR100-24-125/RD	M24	125	2500	200	125,78 €
<b>With 80x80mm mounting plate</b>					
PDR100-80-80/RD	4x8.5mm holes		2500	200	122,18 €

Dimensions in mm


**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

## Our other products



LVT

Miniature motorised actuator 4A, 4 ampers



IN1

Internal gear, Machined plastic (delrin)



BIM

Indexing plunger mini, miniature



H02

Single needle roller universal joint, Heavy duty



RAG

Roller guide,



RPCpl

Swivel castor with double brake, Steel - Polyamide



H0

Crossed helical gear crossed axis at 90°, Steel 20NCD2



T5\_11

T type timing pulley, T5 aluminium



GBMz

Cylindrical ballscrew nut, Cylindrical nut -



PRF4545

Standard stainless steel profile, 45 x 45



CLB\_T

Die cast zinc clamping lever - male, Zamak



TBbutee

Axial thrust bearing, Steel balls

## Complementary products



RIMtce

Locking castor, with central hole



RIMple

Locking castor, with mounting plate