


**- Levelling support****- Materials:**

Base and rod: zinc plated or stainless steel 1.4301 (304)

Base: NBR rubber (Shore hardness 80)

**- Ø80 and Ø100mm bases available****- Supplied with 2 nuts, 1 flat washer and 1 brake washer****Uses****- Laboratory furniture****- Medical and food industries****Note**

- Values for static load given at 50% of rod length. With dynamic or vibrating loads, value will be lower.



stainless steel  
version

**DISCOUNTS**

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØD	M	B	A	A/F	G	H	Static load (N)	Stock*	Price each 1 to 5
<b>Steel</b>										
PFM80-12-75	80	M12	75	28	8	25	103	4500	✓	30,74 €
PFM80-14-100	80	M14	100	28	9	25	128	4500	-	33,97 €
PFM100-12-75	100	M12	75	31	8	28	106	9000	-	32,99 €
PFM100-14-125	100	M14	125	31	9	28	156	9000	-	34,51 €
PFM100-16-125	100	M16	125	31	10	28	156	9000	✓	35,99 €
PFM120-20-125	120	M20	125	35	13	32	160	11000	-	54,67 €
<b>Stainless steel</b>										
PFM80-12-75/SS	80	M12	75	28	8	25	103	4500	✓	52,98 €
PFM80-14-100/SS	80	M14	100	28	9	25	128	4500	✓	56,48 €
PFM100-12-75/SS	100	M12	75	31	8	28	106	9000	-	60,02 €
PFM100-14-125/SS	100	M14	125	31	9	28	156	9000	-	62,94 €
PFM100-16-125/SS	100	M16	125	31	10	28	156	9000	✓	67,48 €
PFM120-20-125/SS	120	M20	125	35	13	32	160	11000	-	76,71 €

\*Depending on availability - Dimensions in mm

## Our other products



QNUP  
Single row cylindrical roller bearing, 1 fixed inner flange and 1 fr...



HTD3M\_09  
HTD Heavy duty timing pulley, HTD3 Aluminium



BLHB20  
Right angled gearbox, bored shafts, up to 1.77 Nm



T5-16ECO  
T type timing pulley, Economy range - T5 aluminium



SDG  
Adjustable guide support bracket, Plastic



SSB  
Stainless steel bevel gear, 1:1



ETP  
Modular handle for aluminium profile, Modular handle



SH2  
Parallel axis helical gear, Machined plastic (delrin)



PSG05  
Spur gear - precision range, Case hardened



INS\_SS  
Self tapping stainless steel insert, 316



RURt  
Swivel castor with central hole,



PW\_PWG3  
Worm - precision range, Steel

## Complementary products

...