

- **Levelling foot**
- **Materials:**
 - Base and spindle: zinc plated or stainless steel 1.4301 (304)
 - Base: NBR rubber (Shore hardness 80)
- Ø80 and Ø100mm bases available
- Supplied with 2 nuts, 1 flat washer and 1 brake washer

Stainless steel version




Uses

- Laboratory furniture
- Medical and food industries

Note

- Values for static load given at 50% of spindle length. With dynamic or vibrating loads, value will be lower.



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØD	M	B	A	A/F	G	H	Static load (N)	Stock*	Price each 1 to 5
Steel foot										
PFM80-12-75	80	M12	75	28	8	25	103	4500	✓	36,01 €
PFM80-14-100	80	M14	100	28	9	25	128	4500	-	39,78 €
PFM100-12-75	100	M12	75	31	8	28	106	9000	-	38,62 €
PFM100-14-125	100	M14	125	31	9	28	156	9000	-	40,42 €
PFM100-16-125	100	M16	125	31	10	28	156	9000	✓	42,16 €
PFM120-20-125	120	M20	125	35	13	32	160	11000	-	64,04 €
Stainless steel foot										
PFM80-12-75/SS	80	M12	75	28	8	25	103	4500	✓	62,07 €
PFM80-14-100/SS	80	M14	100	28	9	25	128	4500	-	66,19 €
PFM100-12-75/SS	100	M12	75	31	8	28	106	9000	-	70,32 €
PFM100-14-125/SS	100	M14	125	31	9	28	156	9000	-	73,73 €
PFM100-16-125/SS	100	M16	125	31	10	28	156	9000	✓	79,06 €
PFM120-20-125/SS	120	M20	125	35	13	32	160	11000	-	89,89 €

*Depending on availability - Dimensions in mm