


## MAX22 Torque from 0.07 to 0.2 Nm


- Type of gearbox: spur gear
- Bearings: self lubricating bushes
- Avg angular backlash: 2° to 3°
- Max axial load: 15N
- Max radial load at 5 mm from fixing surface: 35 N
- Working temperature: -5 to 65 °C
- Weight: 104g min



### Accessories

- ESCON-4Q-50/5 (servo-amplifier, tome 2 p.284)
- NANODC-1Q-30/3 (speed controller, tome 2 p.282)
- Power supplies: ALIDR30-12 and ALIDR30-24 (tome 2 p.280)

Replaces the MAX30



Wire length: 150 mm ±5  
Stripped and tinned ends: 4 mm ±1

### DISCOUNTS

Qty	1+	6+	10+
Disc. List	-7%	On request	

Part number	Ratio	N° of stages	Efficiency	L1 (mm)	No-load speed (rpm)	Speed under load (rpm)	Nominal torque (Nm)	Nominal current (A)	Price each 1 to 5
<b>12 V version</b>									
MAX22-12-015	15:1	3	73%	54,9	356	176	0,07	0,30	251,54 €
MAX22-12-100	100:1	4	66%	57,4	53	47	0,10	0,08	290,77 €
MAX22-12-200	200:1	5	59%	62,4	27	23	0,20	0,09	300,58 €
<b>24 V version</b>									
MAX22-24-015	15:1	3	73%	54,9	435	252	0,07	0,18	251,54 €
MAX22-24-100	100:1	4	66%	57,4	65	58	0,10	0,05	293,30 €
MAX22-24-200	200:1	5	59%	62,4	33	29	0,20	0,05	300,58 €


Dimensions in mm

# Motor-gearboxes 12 and 24 V **DC**

Torque from 0.075 to 0.6 Nm


**MAX26**

- Gearbox type : spur gear
- Precious metal brushes
- Bearing: self lubricating
- Max axial load: 30N
- Min axial backlash: 0.03mm
- Max axial backlash: 0.2mm
- Max radial load: 50N at 5mm from flange
- Press fit force: 500N
- Angular backlash (no load): 2°
- Angular backlash (under load): 3°
- Working temp: from -5° to 65°C
- Input stage: Tufinol
- Output stage: Steel
- Weight: 181g



## Accessories

- NANODC-1Q-30/3 (tome 2 p.282)
- ESCON-4Q-50/5 (tome 2 p.284)
- Power supply ALIDR30-12 and ALIDR30-24 (tome 2 p.280)



## DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-7%	On request

Part number	Reduction	N° of stages	Max efficiency	L1 (mm)	No-load speed (rpm)	Speed under load (rpm)	nominal torque (Nm)	nominal current (A)	Price each 1 to 5
<b>12V Version</b>									
MAX26-12-006	6	2	0,81	62,4	740	457	0,08	0,63	337,70 €
MAX26-12-010	10	2	0,81	62,4	444	311	0,10	0,50	337,70 €
MAX26-12-018	18	3	0,73	67,9	247	155	0,20	0,61	351,92 €
MAX26-12-030	30	3	0,73	67,9	148	115	0,20	0,37	351,92 €
MAX26-12-060	60	4	0,66	70,4	74	47	0,60	0,61	367,92 €
MAX26-12-100	100	4	0,66	70,4	44	35	0,60	0,37	367,92 €
MAX26-12-200	200	5	0,59	72,3	22	19	0,60	0,22	376,81 €
MAX26-12-500	500	6	0,53	75,3	9	8	0,60	0,11	387,49 €
<b>24V Version</b>									
MAX26-24-006	6	2	0,81	62,4	752	459	0,08	0,25	337,70 €
MAX26-24-010	10	2	0,81	62,4	451	310	0,10	0,25	337,70 €
MAX26-24-018	18	3	0,73	67,3	251	154	0,20	0,31	351,92 €
MAX26-24-030	30	3	0,73	67,3	150	116	0,20	0,19	351,92 €
MAX26-24-060	60	4	0,66	70,4	75	46	0,60	0,31	367,92 €
MAX26-24-100	100	4	0,66	70,4	45	35	0,60	0,19	367,92 €
MAX26-24-200	200	5	0,59	72,3	22	20	0,60	0,11	376,81 €
MAX26-24-500	500	6	0,53	75,9	9	8	0,60	0,053	387,49 €

Dimensions in mm