



Self-compensating shock absorber

Not adjustable

MC

- MC25 and MC75: integrated stroke end stop and noise reducing buffer
- Working temperature 0 to +65°C
- Materials:
 - Body: blackened steel
 - Rod: stainless steel
 - Buffer: steel with elastomer insert (MC25 and MC75 only)




Accessories


- See stroke end stop and universal flange

Info.


- MC150: to avoid damaging the EPDM membrane **do not turn the rod**
- For better heat dissipation, do not paint shock-absorbers



MC25



MC75



MC150M

DISCOUNTS

Qty	1+	4+	6+
Disc.	List	-10%	On request

Part number	Effective Weight (kgme)		Max capacity (Nm)		Return spring force (N)	Rod reset time (S)	Max. side load angle	Price each 1 to 3
	Min	Max	Per cycle W3	Per hour W4				
MC25-ML	0,7	2,2	2,8	22600	3-6	0,3	2°	✓ 88,72 €
MC25-M	1,8	5,4	2,8	22600	3-6	0,3	2°	✓ 74,79 €
MC25-MH	4,6	13,6	2,8	22600	3-6	0,3	2°	✓ 74,79 €
MC75-M1	0,3	1,1	9,0	28200	4-9	0,3	2°	- 119,97 €
MC75-M2	0,9	4,8	9,0	28200	4-9	0,3	2°	✓ 119,97 €
MC75-M3	2,7	36,2	9,0	28200	4-9	0,3	2°	✓ 119,97 €
MC150-M	0,9	10,0	20,0	34000	3-8	0,4	4°	✓ 158,92 €
MC150-MH	8,6	86,0	20,0	34000	3-8	0,4	4°	✓ 158,92 €
MC150-MH2	70,0	200,0	20,0	34000	3-8	0,4	4°	- 158,92 €

*Depending on availability - Dimensions in mm

Our other products



DCA

Suction cup, 1.5 bellows, natural rubber



MDB_MTB

Moulded plastic bevel gear (nylon), 3:1



RCX-6

Spherical tilt washer - DIN6319, convex



NT91

Spur gear coaxial gearbox, from 10 to 35 Nm - Inline



BH01

Single housed bearing, Bearing fitted with adhesive



RBGpl

Swivel castor with double brake, Steel - grey rubber




TK

Topball self-aligning linear bearing, Topball self-aligning



PTAF100-PAMF100

Articulated fixable foot with pressed base Ø100, Ø 100



G0

Steel spur gear, Steel 20NCD2



QNUP

Single row cylindrical roller bearing, 1 fixed inner flange and 1 fr...



SSB

Stainless steel bevel gear, 1:1



PSG1S

Spur gear - precision range, Stainless steel 303

Complementary products




RMSA

Adjustable shock-absorber, Adjustable



STC

Shock Absorber - stop collar, Universal flange



MF

Shock Absorber -universal flange, Universal fixing



DZY

Cylindrical stop, Steel