



Self-compensating shock absorber

Not adjustable

MC

- MC25 and MC75: integrated stroke end stop and noise reducing buffer
- Working temperature 0 to +65°C
- Materials:
 - Body: blackened steel
 - Rod: stainless steel
 - Buffer: steel with elastomer insert (MC25 and MC75 only)




Accessories


- See stroke end stop and universal flange

Info.


- MC150: to avoid damaging the EPDM membrane **do not turn the rod**
- For better heat dissipation, do not paint shock-absorbers



MC25



MC75



MC150M

DISCOUNTS

| | | | |
|-------|------|------|------------|
| Qty | 1+ | 4+ | 6+ |
| Disc. | List | -10% | On request |

| Part number | Effective Weight (kgme) | | Max capacity (Nm) | | Return spring force (N) | Rod reset time (S) | Max. side load angle | Price each 1 to 3 |
|-------------|-------------------------|-------|-------------------|-------------|-------------------------|--------------------|----------------------|-------------------|
| | Min | Max | Per cycle W3 | Per hour W4 | | | | |
| MC25-ML | 0,7 | 2,2 | 2,8 | 22600 | 3-6 | 0,3 | 2° | ✓ 88,72 € |
| MC25-M | 1,8 | 5,4 | 2,8 | 22600 | 3-6 | 0,3 | 2° | ✓ 74,79 € |
| MC25-MH | 4,6 | 13,6 | 2,8 | 22600 | 3-6 | 0,3 | 2° | ✓ 74,79 € |
| MC75-M1 | 0,3 | 1,1 | 9,0 | 28200 | 4-9 | 0,3 | 2° | - 119,97 € |
| MC75-M2 | 0,9 | 4,8 | 9,0 | 28200 | 4-9 | 0,3 | 2° | ✓ 119,97 € |
| MC75-M3 | 2,7 | 36,2 | 9,0 | 28200 | 4-9 | 0,3 | 2° | ✓ 119,97 € |
| MC150-M | 0,9 | 10,0 | 20,0 | 34000 | 3-8 | 0,4 | 4° | ✓ 158,92 € |
| MC150-MH | 8,6 | 86,0 | 20,0 | 34000 | 3-8 | 0,4 | 4° | ✓ 158,92 € |
| MC150-MH2 | 70,0 | 200,0 | 20,0 | 34000 | 3-8 | 0,4 | 4° | - 158,92 € |

*Depending on availability - Dimensions in mm

Our other products



T39_T49

Extension spring in metre length stainless steel, by the metre



GCL

Linear ball slide - Stainless steel balls, Chariot - from 516 N to 8...



ZBconique

Machined plastic bevel gear , 1:1



PRF_ROUL

Castor for aluminium profile, No brake



BAC105

Storage bin, 8mm




TBD

Manual lead screw table with opposing threads, 5kg




MFBSC

Stainless steel flexible bellows coupling, Stainless steel - with cl...



RPP5

RPP heavy duty timing belt, RPP5



T5M_T10M

T type timing belt per metre, T10 Steel cored polyurethane



UTKpwrr

V shaped channel UtiliTrak®, V rail



LINK64

Synchronous AC Motor and- gearbox , from 1.3 to 6Nm



J66

Spur gear coaxial gearbox, from 0.90 to 2.80 Nm - Inline

Complementary products




RMSA

Adjustable shock-absorber, Adjustable




STC

Shock Absorber - stop collar, Universal flange



MF

Shock Absorber -universal flange, Universal fixing



DZY

Cylindrical stop, Steel