


# Magnetic stud with central hole



## PLC

## Ferrite

- Cup mounted Ferrite magnet with smooth bored hole
- Working temperature: -50°C to +100°C
- Good corrosion resistance
- Good mechanical resistance



### Uses

- Mounting of objects where space is limited or mounting notice boards, protective covers etc
- Positioning of stops or inserts used in moulding machines

### DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request


Part number	ØD	H	Ød	ØA	F (daN)	Weight (g)	Stock*	Price each 1 to 5
PLC50-10	50	10	8,5	22,0	18	85	✓	8,56 €
PLC63-14	63	14	6,5	24,0	29	197	✓	16,32 €
PLC80-18	80	18	6,5	11,5	54	458	✓	31,70 €

\*Depending on availability - Dimensions in mm

# PLT Magnetic stud with threaded hole

## Ferrite

- Cup mounted Ferrite magnet with smooth bored hole
- Working temp.: -50°C to +100°C
- Good corrosion resistance
- Good mechanical resistance



### Uses

- Fastening: protective casing, tool machines, support cables...
- Positioning: stops, inserts...
- Gripping: inaccessible places, transport

### DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	L	H	Ød	ØM	F (daN)	Weight (g)	Stock*	Price each 1 to 5
PLT25-15	25	15	7	8	M4	4,0	22	✓	5,10 €
PLT32-15	32	15	7	8	M4	8,0	32	✓	6,18 €
PLT40-18	40	18	8	10	M5	12,5	60	✓	8,29 €
PLT50-22	50	22	10	12	M6	22,0	110	✓	10,05 €
PLT63-30	63	30	14	15	M8	35,0	240	✓	18,79 €
PLT80-34	80	34	18	20	M10	60,0	520	-	33,24 €
PLT100-42	100	42	22	22	M12	90,0	940	-	78,80 €


\*Depending on availability - Dimensions in mm

## Our other products



CHA35

Hinge for aluminium profile, Hinge



G0

Steel spur gear, Steel 20NCD2



APB\_BOU

Protective cap, Safety cap



CHA38\_SS

Stainless steel face frame hinge, Surface mount



GE1006

Elastic ringed latch, Hooks into a slot



TBE12

Economic mini-table with trapezoidal lead screw, 2kg



VPRA\_M

Handwheel with handle, Thermosetting plastic - galvanised steel hub



PTA40

Articulated foot with solid base foot Ø 40, 30000N



NDS20

Double cross clamp, Crossed



BPHRF

Ball transfer unit housed spring loaded, High



UGAC\_UGET

Actuator guide kit, Coupling for threaded cylinder end



BPHR

Ball transfer unit housed spring loaded, High

## Complementary products



VAP

Magnetic stud with central hole, With central hole



PLC\_PLT

Magnetic stud with threaded hole, With threaded hole