



# Self-compensating shock absorber

Not adjustable

MC

- MC25 and MC75: integrated stroke end stop and noise reducing buffer
- Working temperature 0 to +65°C
- Materials:
  - Body: blackened steel
  - Rod: stainless steel
  - Buffer: steel with elastomer insert (MC25 and MC75 only)




## Accessories


- See stroke end stop and universal flange

## Info.


- MC150: to avoid damaging the EPDM membrane **do not turn the rod**
- For better heat dissipation, do not paint shock-absorbers



MC25



MC75



MC150M

## DISCOUNTS

Qty	1+	4+	6+
Disc.	List	-10%	On request

Part number	Effective Weight (kgme)		Max capacity (Nm)		Return spring force (N)	Rod reset time (S)	Max. side load angle	Price each 1 to 3
	Min	Max	Per cycle W3	Per hour W4				
MC25-ML	0,7	2,2	2,8	22600	3-6	0,3	2°	✓ 88,72 €
MC25-M	1,8	5,4	2,8	22600	3-6	0,3	2°	✓ 74,79 €
MC25-MH	4,6	13,6	2,8	22600	3-6	0,3	2°	✓ 74,79 €
MC75-M1	0,3	1,1	9,0	28200	4-9	0,3	2°	- 119,97 €
MC75-M2	0,9	4,8	9,0	28200	4-9	0,3	2°	✓ 119,97 €
MC75-M3	2,7	36,2	9,0	28200	4-9	0,3	2°	✓ 119,97 €
MC150-M	0,9	10,0	20,0	34000	3-8	0,4	4°	✓ 158,92 €
MC150-MH	8,6	86,0	20,0	34000	3-8	0,4	4°	✓ 158,92 €
MC150-MH2	70,0	200,0	20,0	34000	3-8	0,4	4°	- 158,92 €

\*Depending on availability - Dimensions in mm

## Our other products



BCTH

Mushroom headed button Hygienic Usit®, With female thread and high ...



RPCtc

Swivel castor with central hole, Steel - Polyamide



MFBS

Stainless steel flexible bellows coupling, Stainless steel - with se...



DOMI30

Accessories, Fixing kit



RJUM01

Closed polymer Drylin® R bearing, Drylin® R



VBFP

Small 6 lobe threaded handle - female, Duroplast - Brass



ZBconique

Machined plastic bevel gear, 1:1



KSM

Cylindrical steel nut, Steel - 1 thread



GE32

Sprung toggle latch with connecting link, Standard



BAN

Angular clamp, Adjustable



M1


Worm and wheel set, Machined plastic (delrin)



EHD08-9

Internal epicyclic servo reducers, from 35 to 50 Nm

## Complementary products



MF

Shock Absorber -universal flange, Universal fixing



STC

Shock Absorber - stop collar, Universal flange



DZY

Cylindrical stop, Steel



DPAR\_DKON

Progressive stop, Steel