


Cylindrical magnet

SmCo

PLM

- **Smooth finish, shielded system**
- Do not press fit directly into an iron support as a magnetic short circuit will reduce the adhesive force
- Suitable for use in spot welding machines.
- Dimension "H" can be reduced with no loss of adhesive force
- Max working temp : +200°C
- **Material, finish**
Galvanised steel body,
Magnetic core SmCo



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request



Part number	ØD	L	H	Attraction force (N)	Distance to iron wall/mm	Weight (g)	Stock*	Price each 1 to 5
PLM6-20/SC	6	20	10,0	8	1,5	4,5	✓	6,44 €
PLM8-20/SC	8	20	10,0	22	1,5	8,0	✓	8,11 €
PLM10-20/SC	10	20	8,0	40	2,0	12,0	✓	9,94 €
PLM13-20/SC	13	20	6,0	60	2,5	20,0	-	13,18 €
PLM16-20/SC	16	20	2,0	125	3,0	30,0	-	17,95 €
PLM20-25/SC	20	25	5,0	250	4,0	60,0	-	29,36 €
PLM25-35/SC	25	35	7,0	400	5,0	134,0	-	66,14 €
PLM32-40/SC	32	40	4,5	600	6,0	251,0	-	120,64 €

Threaded cylindrical magnet

NdFeB

PLM

- **Shielded system**
- Suitable for mounting in steel or iron supports
- Can also be used as blind-hole magnets
- Max working temp : +80°C
- **Material, finish**
Galvanised steel body,
Magnetic core NdFeB




DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request


Part number	ØD	ØD1	L	T	Attraction force (N)	Weight (g)	Stock*	Price each 1 to 5
PLM8-12/N	8	M3	12	5	12	7	✓	7,49 €
PLM10-16/N	10	M4	16	7	24	8	✓	8,59 €
PLM13-18/N	13	M4	18	7	60	18	✓	9,82 €
PLM16-20/N	16	M4	20	7	90	30	✓	10,42 €
PLM20-25/N	20	M5	25	9	135	60	-	18,02 €
PLM25-30/N	25	M6	30	9	190	110	-	38,44 €
PLM35-40/N	35	M8	40	13	300	290	-	66,50 €

Dimensions in mm

Our other products



T type timing belt per metre, T5 Steel cored polyurethane



Closing system for aluminium profile, 90° bracket for spherical end...



Square tube connector, Fixed angle



AT type timing belt per metre, AT5 Steel cored polyurethane



Quarter-turn clamp lock - Clamping plate, Wall mounting




Asynchronous AC Motor, 0.55 to 1.1kW



Worm and wheel gear reducer, up to 298 Nm



Miniature motorised actuator 1A, 1 amper



Worm and wheel set, Machined plastic (delrin)



Brush strip per meter horsehair fibres Ø0.2, Black horsehair



Cap for square tube to be welded, To be welded



Single and dual output gearboxes, Up to 9,1 Nm

Complementary products



Cylindrical holding magnets, Cylindrical holding magnet



Cylindrical magnet, Cylindrical magnet