

Shackle with eye bolt




MDR

Pin diameters 5-20mm

- **Lifting shackle**
- Marked with pin diameter, SWL and CE mark
- Material:
Shackle: Steel Fe430B zinc treated

Info.

- SWL: SAFE WORKING LOAD.
The Safe Working Load is calculated by dividing the Breaking Strength by a factor of safety of 5.
- **Not sold individually, please contact us for details.**



DISCOUNTS

Qty	1+	5+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	Pin ØD	A	B	ØC	ØE	F	SWL (kg)	Weight (kg)	Stock*	Price each 1 to 4
MDR1-05	5	8	18	13	6	23	100	0,020	✓	2,04 €
MDR1-06	6	12	25	14	6	29	160	0,040	✓	2,45 €
MDR1-08	8	15	32	18	8	37	250	0,070	✓	2,98 €
MDR1-10	10	18	38	22	10	41	400	0,140	✓	3,76 €
MDR1-12	12	26	50	27	12	56	630	0,260	✓	5,94 €
MDR1-14	14	27	56	29	14	57	800	0,370	✓	7,28 €
MDR1-16	16	31	64	35	17	64	1000	0,560	✓	9,76 €
MDR1-18	18	32	70	36	19	65	1300	0,710	✓	13,50 €
MDR1-20	20	38	78	40	20	69	1600	0,940	✓	17,03 €

*Depending on availability - Dimensions in mm

Our other products



PLC_PLT

Magnetic stud with threaded hole, With threaded hole



H1

Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



CF

Cam follower,
Standard - steel



KKB-AR

Linear bearing with
inclined ball tracks,
Standard loads / -20°
+20...



INS

Self tapping steel
insert, Steel



E60

Right angle helical
reducers, from 4.50 to
62 Nm



RFVbr

Stainless steel
reaction arm,
Reaction arm



PRES

Manual workbench
press accessory for
PRES-3HR end
PRES-4HR, Set of s...



GAL21

Conveyor wheel,
Plastic



SVG

Adjustable latch
clamp with strike



PTA40

Articulated foot with
solid base foot Ø 40,



LRRA

Latch with locking
system, Aluminium

Complementary products




MDR_SS

Stainless steel Dee
shackle with eye bolt,
Stainless steel



MLY

Bow shackle with eye
bolt, Steel



CAB

Galvanised steel
cable, Galvanised
steel



TAC

Rigging screw
(hook/eye), Steel