



Plastic bevel gear

Moulded nylon 6

Ratio
1.5:1
4:1


- Module 2 to 3
- Moulded parts
- Material:
Nylon 6 reinforced with 30% glass fibre

Options

- We are unable to modify these parts



Info.

- The 2 bevels should form a matching pair
- Moulded pre-bore must be machined to suit the application
- *Pilot bore dimension given as a guide only



*ØA:
pilot bore
requires
finishing*

Economy range



DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Teeth		ØDe	ØDp	B	F	ØDn	ØA*	dm	L	Lm	Stock*	Price each 1 to 9
	Z	Module											
Ratio 4:1													
MFB2.5-16	16	2,5	44,9	40	30,5	18	32	15	92,6	29,0	11,7	✓	12,39 €
MFB2.5-64	64	2,5	161,2	160	35,0	18	80	20	48,8	30,0	16,0	✓	55,24 €
MFB3-16	16	3,0	53,8	48	32,0	20	35	10	108,0	30,0	11,1	✓	23,14 €
MFB3-64	64	3,0	193,5	192	42,0	20	60	19	58,8	36,0	22,0	✓	61,38 €
Ratio 1,5:1													
MHB2-20	20	2,0	43,3	40	23,0	10	30	8	43,3	23,0	10,2	-	12,54 €
MHB2-30	30	2,0	62,2	60	27,0	10	50	11	40,6	27,5	15,2	-	18,34 €


*Depending on availability - Dimensions in mm

Our other products




MDR

Dee shackle with eye bolt, Steel



IN1

Internal gear, Machined plastic (delrin)



M1

Worm and wheel set, Bronze



PDM_PDV

Detectable plastic palm grip, by metal detectors



RT25

Self-centering flanged locking assembly, Medium/high torque



HS

Hexagonal spacer, Stainless steel 303



PRF JL4

Lip seal for panel, Door seal - Ø 4mm



NT63

Spur gear coaxial gearbox, from 8 to 20 Nm - In-line



BTE

Universal tension arm, For standard



PSEC

Security pull handle, Thermoplastic



PLM-SC

Magnetic stud with central countersunk



PGT

Sliding profile, Sliding panel support

Complementary products