




Flat magnet

SmCo

PLM

- Flat gripping magnet, shielded case
- Flat gripping magnets with an SmCo core have three to five times the adhesive force of AlNiCo or hard ferrites
- Max working temp +200°C
- **Material, finish**

Galvanised steel body,
Magnetic core SmCo



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	ØD1	ØD2	L	L1	Attraction force (N)	Stock*	Price each 1 to 5
PLM6-4-M3/SC	6 ^{±0,15}	6	M3	11,5	4,5	5	✓	5,14 €
PLM8-4-M3/SC	8 ^{±0,15}	6	M3	11,5	4,5	11	✓	5,95 €
PLM10-4-M3/SC	10 ^{±0,15}	6	M3	11,5	4,5	20	✓	8,27 €
PLM13-4-M3/SC	13 ^{±0,15}	6	M3	11,5	4,5	40	-	9,77 €
PLM16-4-M4/SC	16 ^{±0,15}	8	M4	11,5	4,5	60	✓	12,67 €
PLM20-6-M4/SC	20 ^{±0,15}	8	M4	13,0	6,0	90	-	20,38 €
PLM25-7-M4/SC	25 ^{±0,15}	8	M4	14,0	7,0	150	✓	31,03 €
PLM32-7-M5/SC	32 ^{±0,20}	10	M5	15,5	7,0	220	-	46,40 €

Dimensions in mm


Flat hard ferrite magnet

With milled bore

PLM

- **Shielded system**
- Max working temp : +200°C
- **Material, finish**

Galvanised steel body,
Hard ferrite magnetic core



INCREASED STOCK

DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	ØD1	ØD2	H	Attraction force (N)	Weight (g)	Stock*	Price each 1 to 5
PLM16-4/F	16 ^{±0,15}	3,3	7	4,5	14	4	✓	4,20 €
PLM20-6/F	20 ^{±0,15}	4,2	9	6,0	27	9	✓	4,42 €
PLM25-7/F	25 ^{±0,15}	5,5	11	7,0	36	17	✓	4,70 €
PLM32-7/F	32 ^{±0,20}	5,5	11	7,0	72	27	✓	5,11 €
PLM40-8/F	40 ^{±0,20}	5,5	11	8,0	90	52	✓	6,69 €

Dimensions in mm

Our other products



HLU
Spoked handwheel
without handle,
Aluminium



BAN
Angular clamp,
Adjustable



PSG125S
Spur gear - precision
range, Stainless steel
316



ACLCHARJ
Hinge for aluminium
profile, Adjusts in 2
directions



H1
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2




SME
Male rod ends ,
Stainless steel / PTFE



PTAF100-PAMF100
Articulated fixable
foot with pressed
base Ø100, Ø 100



PPF
Indexing plunger with
flange, with drilled
flange



PRZ
Wear strip for slat top
chain, Z profile to be



YG4
HEAVY DUTY spur
gear, Steel 35NCD6



BOX-CSss
Hose clamp, Box set
of stainless steel hose



PRF_T
Corner reinforcement,
Corner reinforcement

Complementary products



PLM-16A
Magnetic stud with
threaded hole, With
threaded hole



PLM-SC
Magnetic stud with
central countersunk
hole, With milled bore