

Anti-vibration machine mount


New

PMB

Format Oval base plate

- With 2 fixing holes
- Loads shown refer to permissible static vertical dead load
- Materials :
Natural rubber
Steel structure

NEW !






Application

- These elements are ideal for low frequencies because the rubbers are available with different hardnesses so that a wide load range can be covered

Info.

- Supplied with support disc for better load distribution



DISCOUNTS

| Qty | 1+ | 6+ | 10+ | 20+ |
|-------|------|-----|------|------------|
| Disc. | List | -5% | -10% | On request |

| Part number | ØD | H1 | H | E | L | ØM | ØA | S | Hardness shore | Load max (daN) | Deflexion | Price each 1 to 5 |
|---------------|-----|----|----|-----|-----|-----|------|-----|----------------|----------------|-----------|-------------------|
| PMB40-M6-35 | 40 | 18 | 20 | 52 | 64 | M6 | 6,2 | 2 | 35 | 2,5 | 2,5±0,5 | 9,83 € |
| PMB40-M6-45 | 40 | 18 | 20 | 52 | 64 | M6 | 6,2 | 2 | 45 | 5 | 2,5±0,5 | 9,83 € |
| PMB40-M6-60 | 40 | 18 | 20 | 52 | 64 | M6 | 6,2 | 2 | 60 | 10 | 2,5±0,5 | 9,83 € |
| PMB60-M6-45 | 60 | 22 | 24 | 76 | 90 | M6 | 6,2 | 2 | 45 | 15 | 3,5±0,5 | 17,04 € |
| PMB60-M6-60 | 60 | 22 | 24 | 76 | 90 | M6 | 6,2 | 2 | 60 | 25 | 3,5±0,5 | 17,04 € |
| PMB60-M6-75 | 60 | 22 | 24 | 76 | 90 | M6 | 6,2 | 2 | 75 | 50 | 3,5±0,5 | 17,04 € |
| PMB80-M8-45 | 80 | 25 | 27 | 100 | 120 | M8 | 8,2 | 2 | 45 | 40 | 4,5±0,5 | 23,19 € |
| PMB80-M8-60 | 80 | 25 | 27 | 100 | 120 | M8 | 8,2 | 2 | 60 | 80 | 4,5±0,5 | 23,19 € |
| PMB80-M8-75 | 80 | 25 | 27 | 100 | 120 | M8 | 8,2 | 2 | 75 | 120 | 4,5±0,5 | 23,19 € |
| PMB100-M10-45 | 100 | 25 | 28 | 124 | 148 | M10 | 10,2 | 2,5 | 45 | 75 | 4,5±1 | 30,37 € |
| PMB100-M10-60 | 100 | 25 | 28 | 124 | 148 | M10 | 10,2 | 2,5 | 60 | 160 | 4,5±1 | 30,37 € |
| PMB100-M10-75 | 100 | 25 | 28 | 124 | 148 | M10 | 10,2 | 2,5 | 75 | 220 | 4,5±1 | 30,37 € |
| PMB150-M14-45 | 150 | 35 | 40 | 182 | 214 | M14 | 11,8 | 4 | 45 | 130 | 7±1,5 | 66,64 € |
| PMB150-M14-60 | 150 | 35 | 40 | 182 | 214 | M14 | 11,8 | 4 | 60 | 300 | 7±1,5 | 66,64 € |
| PMB150-M14-75 | 150 | 35 | 40 | 182 | 214 | M14 | 11,8 | 4 | 75 | 400 | 7±1,5 | 66,64 € |

Dimensions in mm

HPC

WEB
04/2024

www.hpceurope.com


Tel. +33(0)4 37 496 496

Our other products



G1

Steel spur gear, Steel
20NCD2



CXS

External circlip
DIN471, external DIN
471



CHMR90

Worm and wheel gear
reducer, up to 540
Nm



CHA1056_U4

Screw-in hinge,
Section 40X40



BPLF

Ball transfer unit light
duty, Light



PGNT

Thermoplastic T
handle, With threaded
spindle




STRIP1000

Sealing brush strip,
1m length



T39_T49

Extension spring in
metre length stainless
steel, by the metre



PRF_PSA

Shaft support for
aluminium profile,



ACLBDB

Closing mechanism
for aluminium profile,



MEP

Revolving handle for
handwheel, Fixed



SFE

Female rod ends,
Stainless steel / PTFE

Complementary products



AZY

Cylindrical elasto
mount, Steel



AZY_SS

Stainless steel
cylindrical elasto
mount, Stainless steel



BZY

Cylindrical elasto
mount, Steel



BZY_SS

Stainless steel
cylindrical elasto
mount, Stainless steel