



# Rubber machine mount



## Square base plate

## PMC

- **With 4 fixing holes**
- Maximum loads are given for a permanent, static vertical load
- Materials:
  - Centre: Natural rubber (60 Shore A)
  - Support: steel

### Uses

- Anti vibration mounting for machines and all types of motors
- Active effective protection for personnel and surroundings from harmful effects of vibrations
- Passive protection of sensitive machines, measuring instruments, equipment and many different types of machines against shocks and vibration.



### DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	ØC	H	ØA	ØG	S	L	B	B1	Max. load (N)	Stock*	Price each 1 to 5
PMC150-M16	150	51,5	110	M16	4,0	12,5	132	168	7800	✓	49,65 €
PMC177-M20	177	63,0	125	M20	4,5	13,0	150	184	16500	-	72,48 €

\*Depending on availability - Dimensions in mm

## Our other products



SH2

Parallel axis helical gear, Steel 20NCD2



WTM

Tightening washer - DIN6340, Steel



BABtss

303 Stainless steel ball pin, 303 Stainless steel



BSM\_LOK

Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...



TRMSS

Spur round rack, Stainless steel - module 1-5



HK

Manual locking clamp, Manual locking clamp LWH




APB\_F

Adjusting rod for clamp - Male, Threaded



AT5M AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane



T5M T10M

T type timing belt per metre, T10 Steel



ACM\_DZ

Clip for bonnet fastener, Clip



BOX-TOR-H

Box set of Nitrile O-rings in nitrile, 3.00 x



M

Bellows cover, Accessory:

## Complementary products



PMC48\_M8

Anti-vibration machine mount, Oval base plate



PCF4

Conical flexible mount, Square base plate