

- With 2 fixing holes
- Loads shown refer to permissible static vertical dead load
- Materials :  
Natural rubber  
Steel structure

NEW!






### Applications

- These elements are ideal for low frequencies because the rubbers are available with different hardnesses so that a wide load range can be covered

### Info

- Supplied with support disc for better load distribution



### DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	ØD	H1	H	E	L	ØM	ØA	S	Hardness shore	Load max (daN)	Deflexion	Price each 1 to 5
PMB40-M6-35	40	18	20	52	64	M6	6,2	2	35	2,5	2,5 <sup>+0,5</sup>	9,93 €
PMB40-M6-45	40	18	20	52	64	M6	6,2	2	45	5	2,5 <sup>+0,5</sup>	9,93 €
PMB40-M6-60	40	18	20	52	64	M6	6,2	2	60	10	2,5 <sup>+0,5</sup>	9,93 €
PMB60-M6-45	60	22	24	76	90	M6	6,2	2	45	15	3,5 <sup>+0,5</sup>	17,21 €
PMB60-M6-60	60	22	24	76	90	M6	6,2	2	60	25	3,5 <sup>+0,5</sup>	17,21 €
PMB60-M6-75	60	22	24	76	90	M6	6,2	2	75	50	3,5 <sup>+0,5</sup>	17,21 €
PMB80-M8-45	80	25	27	100	120	M8	8,2	2	45	40	4,5 <sup>+0,5</sup>	23,42 €
PMB80-M8-60	80	25	27	100	120	M8	8,2	2	60	80	4,5 <sup>+0,5</sup>	23,42 €
PMB80-M8-75	80	25	27	100	120	M8	8,2	2	75	120	4,5 <sup>+0,5</sup>	23,42 €
PMB100-M10-45	100	25	28	124	148	M10	10,2	2,5	45	75	4,5 <sup>+1</sup>	30,67 €
PMB100-M10-60	100	25	28	124	148	M10	10,2	2,5	60	160	4,5 <sup>+1</sup>	30,67 €
PMB100-M10-75	100	25	28	124	148	M10	10,2	2,5	75	220	4,5 <sup>+1</sup>	30,67 €
PMB150-M14-45	150	35	40	182	214	M14	11,8	4	45	130	7 <sup>+1,5</sup>	67,30 €
PMB150-M14-60	150	35	40	182	214	M14	11,8	4	60	300	7 <sup>+1,5</sup>	67,30 €
PMB150-M14-75	150	35	40	182	214	M14	11,8	4	75	400	7 <sup>+1,5</sup>	67,30 €



Dimensions in mm

- With 2 fixing holes
- Maximum loads are given for a permanent, static vertical load
- Materials:  
Centre: Natural rubber (60 Shore A)  
Support: steel



### Uses

- Anti vibration mounting for machines and all types of motors
- Active effective protection for personnel and surroundings from harmful effects of vibrations
- Passive protection of sensitive machines, measuring instruments, equipment and many different types of machines against shocks and vibration.



### DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	ØC	H	ØA	ØG	S	L	B	B1	Max. load (N)	Stock*	Price each 1 to 5
PMC48-M8	48	23	38,0	M8	1,5	6,2	68	81	1900	✓	14,49 €
PMC62-M10	62	30	50,0	M10	3,0	8,2	85	106	3900	✓	20,57 €
PMC92-M12	92	45	73,5	M12	3,0	10,2	110	128	5800	✓	28,01 €
PMC120-M16	120	50	90,0	M16	5,0	16,2	160	190	11500	-	60,61 €
PMC160-M16	160	60	120,0	M16	3,0	16,2	200	235	23000	-	96,60 €

\*Depending on availability - Dimensions in mm



# Anti-vibration rubber machine mount


## Square base plate

## PMC

- **With 4 fixing holes**
- Maximum loads are given for a permanent, static vertical load
- Materials:
  - Centre: Natural rubber (60 Shore A)
  - Support: steel

### Uses

- Anti vibration mounting for machines and all types of motors
- Active effective protection for personnel and surroundings from harmful effects of vibrations
- Passive protection of sensitive machines, measuring instruments, equipment and many different types of machines against shocks and vibration.



### DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	ØC	H	ØA	ØG	S	L	B	B1	Max. load (N)	Stock*	Price each 1 to 5
PMC150-M16	150	51,5	110	M16	4,0	12,5	132	168	7800	✓	57,24 €
PMC177-M20	177	63,0	125	M20	4,5	13,0	150	184	16500	-	83,55 €

\*Depending on availability - Dimensions in mm