


- For joining or closing chains
- Screw to secure
- Fully tighten to ensure safety CE and SWL markings
- Material:
Link : Steel Fe430B zinc treated
Nut: Steel A-42-Fm



Info.

- SWL: safe working load.
The Safe Working Load is calculated by dividing the Breaking Strength by a factor of safety of 5.
- Not sold individually, please contact us for details



DISCOUNTS

Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	L2	L1	L	P	E	SWL (kg)	Weight for 100 pieces (kg)	Stock*	Price each 1 to 9
MRA1-04	4	39,5	31,5	11,5	5,5	12,5	180	1,170	✓	2,60 €
MRA1-05	5	49,5	39,5	13,0	6,5	16,0	280	2,050	✓	2,96 €
MRA1-06	6	57,0	45,0	14,5	7,5	19,0	400	3,450	✓	3,49 €
MRA1-07	7	66,0	52,0	16,0	8,5	21,5	550	5,100	✓	4,40 €
MRA1-08	8	74,0	58,0	17,5	11,0	24,0	700	7,700	✓	5,06 €
MRA1-09	9	80,0	62,0	19,0	11,0	26,0	900	10,250	✓	6,83 €
MRA1-10	10	89,0	69,0	20,5	12,0	29,0	1100	13,700	✓	7,58 €
MRA1-12	12	104,5	80,5	23,5	15,0	33,0	1500	23,200	✓	10,97 €


*Depending on availability - Dimensions in mm

Our other products



BOX-TOR-C

Box set of Nitrile O-rings in nitrile, 3.00 x 1.50mm to 30.20 x 3.00



MR_MMR

Metric section rack, Steel



BPTR

End cap for round tube, Standard



SVT_CH

Screwjack - pivot mounting, Pivoting bracket




PGMT

Pull handle, Stainless steel



SVR30

Screwjack with travelling nut, with moving nut



KS

Keysteel, Steel - Keystock



MPS

Hexagonal spacer, Stainless steel 303



INS_SS

Self tapping stainless steel insert, Stainless steel



SCE

U-shaped cable clamp, Steel



BSM_LOK

Long-Lok spring plunger with internal hexagonal socket,



SLBWSS

Indexing plunger, weldable, Weldable - Stainless steel

Complementary products



MRAeco

Low cost quick link, Steel



MRA_SS

Stainless steel Quick link, Stainless steel



MRASeco

Low cost stainless steel quick link, Stainless steel



CHN_CHNSS

Straight long link chain, Galvanised steel