


Rubber machine mount



PMC


Oval base plate

- With 2 fixing holes
- Maximum loads are given for a permanent, static vertical load
- Materials:
Centre: Natural rubber (60 Shore A)
Support: steel




Uses

- Anti vibration mounting for machines and all types of motors
- Active effective protection for personnel and surroundings from harmful effects of vibrations
- Passive protection of sensitive machines, measuring instruments, equipment and many different types of machines against shocks and vibration.



Anti-vibration



DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	ØC	H	ØA	ØG	S	L	B	B1	Max. load (N)	Stock*	Price each 1 to 5
PMC48-M8	48	23	38,0	M8	1,5	6,2	68	81	1900	✓	12,58 €
PMC62-M10	62	30	50,0	M10	3,0	8,2	85	106	3900	✓	17,85 €
PMC92-M12	92	45	73,5	M12	3,0	10,2	110	128	5800	✓	24,29 €
PMC120-M16	120	50	90,0	M16	5,0	16,2	160	190	11500	-	52,58 €
PMC160-M16	160	60	120,0	M16	3,0	16,2	200	235	23000	-	83,80 €

*Depending on availability - Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



PPCss
Pad eye on mounting plate squarred, Stainless steel




BL15
Right angled gearbox, from 1.10 to 6 Nm



BIM55
Indexing plunger mini, miniature - Stainless steel



PW_PWG1
Wheel - precision range, Bronze



MO
Worm and wheel set, Machined plastic (delrin)



EPE
Wing nuts Hygienic Design®, Narrow



BSM_LOK
Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...




ACLEPP
Right angled bracket for aluminium profile, 2 holes



CHAEpac
Square decorative screwed hinges, carbon fibre



CHV
Mechanical speed variator, from 0,18 to 1,5kW



RAGb
Cylindrical brush track, For gentle conveying and



T10courroie
T type timing belt, T10 Steel cored polyurethane

Complementary products



PMC150_M16
Anti-vibration machine mount, Square base plate



PCF2
Conical flexible mount, Oval base plate



PCF4
Conical flexible mount, Square base plate