


- For joining or closing chains
- Screw to secure
- Fully tighten to ensure safety CE and SWL markings
- Material:  
Link : Steel Fe430B zinc treated  
Nut: Steel A-42-Fm



### Info.

- SWL: safe working load.  
The Safe Working Load is calculated by dividing the Breaking Strength by a factor of safety of 5.
- Not sold individually, please contact us for details




### DISCOUNTS

Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	L2	L1	L	P	E	SWL (kg)	Weight for 100 pieces (kg)	Stock*	Price each 1 to 9
MRA1-04	4	39,5	31,5	11,5	5,5	12,5	180	1,170	✓	2,60 €
MRA1-05	5	49,5	39,5	13,0	6,5	16,0	280	2,050	✓	2,96 €
MRA1-06	6	57,0	45,0	14,5	7,5	19,0	400	3,450	✓	3,49 €
MRA1-07	7	66,0	52,0	16,0	8,5	21,5	550	5,100	✓	4,40 €
MRA1-08	8	74,0	58,0	17,5	11,0	24,0	700	7,700	✓	5,06 €
MRA1-09	9	80,0	62,0	19,0	11,0	26,0	900	10,250	✓	6,83 €
MRA1-10	10	89,0	69,0	20,5	12,0	29,0	1100	13,700	✓	7,58 €
MRA1-12	12	104,5	80,5	23,5	15,0	33,0	1500	23,200	✓	10,97 €

\*Depending on availability - Dimensions in mm

## Our other products



SBS\_M

Single chain supplied by the metre, Stainless steel



PF20

Worm and wheel gear reducer, up to 5 Nm



D-PAR\_SS

Stainless steel elastomeric mount, stainless steel



GP

Spring loaded toggle latch, Standard (GP22-GP23)



COA-COG

Surface mounting plate, Surface mounting plate for ball joint



M1

Worm and wheel set, Hardened steel



CHAGC-AL

Screw-in garnet hinge, Screw-on



PRS30

Stainless steel articulated foot Ø30, Ø 30



PCS37SS

Chain sprocket - Stainless steel, 9.525 (DIN 06B-1)




SLBS

Stainless steel indexing plunger, Stainless steel



CM\_CO

Tools Hygienic Usit® and Hygienic Design®, Protective



RPPM

RPP type belt per metre, RPP14 Steel cored polyurethane

## Complementary products




CHN\_CHNSS

Straight long link chain, Galvanized steel



MRAeco

Low cost quick link, Steel



CHNrb

Warning chain with red and white links, Steel