


Rubber machine mount



PMC


Oval base plate

- With 2 fixing holes
- Maximum loads are given for a permanent, static vertical load
- Materials:
Centre: Natural rubber (60 Shore A)
Support: steel




Uses

- Anti vibration mounting for machines and all types of motors
- Active effective protection for personnel and surroundings from harmful effects of vibrations
- Passive protection of sensitive machines, measuring instruments, equipment and many different types of machines against shocks and vibration.



Anti-vibration



DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	ØC	H	ØA	ØG	S	L	B	B1	Max. load (N)	Stock*	Price each 1 to 5
PMC48-M8	48	23	38,0	M8	1,5	6,2	68	81	1900	✓	12,58 €
PMC62-M10	62	30	50,0	M10	3,0	8,2	85	106	3900	✓	17,85 €
PMC92-M12	92	45	73,5	M12	3,0	10,2	110	128	5800	✓	24,29 €
PMC120-M16	120	50	90,0	M16	5,0	16,2	160	190	11500	-	52,58 €
PMC160-M16	160	60	120,0	M16	3,0	16,2	200	235	23000	-	83,80 €

*Depending on availability - Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



FUSS

Bearing locknut, Self locking locknut - stainless steel lock washer



AT5P_AT10P

Connecting plate for AT type timing belts, AT10



ZBconique

Machined plastic bevel gear, 1:1



COA_COG

Surface mounting plate, Surface mounting plate for ball joint



PAP

Handle for aluminium profile, Ergonomic handle



CHB

Feet, For CHB gearbox



AT10-32ECO

AT type timing pulley, Economy range - AT10 aluminium



FTSN

Supported shaft for linear guide, Steel shaft / Aluminium support



MEB

Moulded plastic bevel gear (nylon), 1:1




E60

Right angle helical reducers, from 4.50 to 62 Nm



DIA

Ring operated locking bolt, with ring



GBMz

Cylindrical ballscrew nut, Cylindrical nut - Multiple starts

Complementary products



PMC150_M16

Anti-vibration machine mount, Square base plate



PCF2

Conical flexible mount, Oval base plate



PCF4

Conical flexible mount, Square base plate