

# Cylindrical Master-Plate® glueable insert Ø38

## MSP38

## Inox 316L


- Glueable stainless steel plate with tapped insert or threaded stud
- Material:  
316L stainless steel

### Applications



- Industrial, transport, building, furnishings

### Info.

- Glue not supplied
- Not supplied individually, contact us for details



Exemple d'application



### DISCOUNTS

Qty	1+	50+	100+	500+
Disc.	List	-10%	-20%	On request

Part number	ØA	ØD	L	Form	Price each 1 to 49
MSP38EB-8-6/SS	38	M8	6,5	Blind tapped	3,11 €
MSP38E-8-6/SS	38	M8	6,5	Nut	3,11 €
MSP38F-6-40/SS	38	M6	40	Thread	3,11 €
MSP38F-8-40/SS	38	M8	40	Thread	3,51 €

Dimensions in mm

## Our other products



HG5-ECO

Eco range Spur gear,  
Steel C45



PT881

Drive sprocket for slat  
top chain, Range 881



CNA-CNG

Right angled  
mounting plate, Right  
angled mounting  
plate for clevis



PARF110

Pressed steel base  
rigid foot, Swivelling  
Ø110



RFK38B

Hypoid gearbox -  
Stainless steel, up to  
200 Nm




RFV50

Stainless steel worm  
and wheel gearbox,  
up to 80 Nm



SHSS

Shoulder screw  
stainless steel 416,  
Pre-treated 416  
stainless steel



LAT4

4A motorised linear  
actuator, 4 amperes



MAX26

Motor-gearbox 12V  
and 24V DC, from  
0,075 to 0,6Nm



CNA-CNG

Right angled  
mounting plate, Right  
angled mounting



SH3

Parallel axis helical  
gear, Steel 20NCD2



BABtss

303 Stainless steel  
ball pin, 303 Stainless  
steel

## Complementary products



MSP3815

Masterplate®  
glueable insert  
rectangular,  
rectangular with

tapped i...



MSP38

Masterplate®  
glueable insert Ø38,  
Cylindrical Ø38 with  
threaded s...



MSP23

Masterplate®  
glueable insert Ø23,  
Cylindrical Ø23 with  
threaded s...



MSP3815

Masterplate®  
glueable insert  
rectangular,  
rectangular with nut