

Levelling foot stainless steel **for robot**

PMN

Max load up to 45 000N

- Foot with stainless steel base plate

- Materials:


- AISI 304 stainless steel base
- AISI 304 stainless steel rod
- NBR FDA-approved rubber foot, 90° Shore hardness

Advantages


- Excellent value for money
- Foot offers exceptional resistance to machine slippage or movement

Installation

- Position the levelling foot at the intended location for your machine
- Once the levelling foot and the machine are correctly positioned, drill into the floor using the through-hole located between the rod and the base
- Insert a threaded rod and secure it with resin or a wall plug
- This results in a levelling foot that is fully self-supporting, with no visible holes, and which can be adjusted for height



Installation



DISCOUNTS

Qty	1+	5+	8+
Disc.	List	-5%	On request

Références	B	A	M	G	H	H1	ØD	ØD1	Max load (N)	Price each 1 to 4
PMN120-160/SS	121	31	M30x1.5	18	152	160	120	19	45000	

Dimensions in mm

Our other products



ACL-PLAngle
Joining plate for
aluminium profile,
Angle connection



SVG
Adjustable latch
clamp with strike
plate, Stroke from
106,7mm to 121...



NDS14C
Angular connector,
Universal angular
connector




CHAGC-AL
Screw-in garnet
hinge, Screw-on



PSG25
Spur gear - precision
range, Pre-hardened
Steel 35NCD6



GLT3-76
Telescopic drawer,



LSM
Stainless steel 316L
leadscrew, Stainless
steel - 1 thread



SCR
Suction cup threaded
insert, Insert for
suction cup - Socket
screw



PVL
Small lobed handle,
Polyamide



BLHB40
Right angled gearbox,
bored shafts, up to
10.3 Nm



SSDB
Stainless steel bevel
gear, 2:1



HTD8M_50
HTD Heavy duty
timing pulley, HTD8
Cast iron or Steel

Complementary products