

Rectangular Master-Plate® glueable insert

316L stainless steel

MSP

- Glueable stainless steel plate with tapped insert or threaded stud
- Material:
316L stainless steel

Applications

- Industrial, transport, building, furnishings




Info.

- Glue not supplied
- Not supplied individually, contact us for details

316L stainless steel



316L stainless steel



Typical application

DISCOUNTS


Qty	1+	50+	100+	500+
Disc.	List	-10%	-20%	On request

Part number	A	B	ØD	L	Form	Price each 1 to 49
MSP3815T-6-5/SS	38	15	M6	5	Tapped	5,82 €
MSP3815E-5-4/SS	38	15	M5	4	Nut	2,05 €
MSP3815E-6-5/SS	38	15	M6	5	Nut	2,31 €
MSP3815E-8-6/SS	38	15	M8	6,5	Nut	2,50 €
MSP3815F-5-12/SS	38	15	M5	12	Thread	2,16 €
MSP3815F-5-16/SS	38	15	M5	16	Thread	2,21 €
MSP3815F-6-16/SS	38	15	M6	16	Thread	2,24 €
MSP3815F-6-20/SS	38	15	M6	20	Thread	2,29 €

Dimensions in mm


0 825 88 6000
Service 0,15 € / min
+ prix appel

Our other products



PO

Pull handle - Multi-sector, Tapped recessed insert



KSM

Cylindrical steel nut, Steel - 1 thread



SUPCC

Self-centering clamping hub steel, With lock nut



PSG055

Spur gear - precision range, Stainless steel 303



GTCCS

Belt tensioner, For use in hostile environments



PO

Pull handle - Multi-sector, Smooth hole



PRF_P

Anchor foot for 45x45 profile, Anchor foot



PRF_ROUL_F_

Castor for aluminium profile, With brake




YG1

HEAVY DUTY spur gear, Steel 35NCD6



MDB_MTB_

Moulded plastic bevel gear (nylon), 3:1



CFC

Spring loaded position switch, Electric



APBC

Circular rod, Round rod

Complementary products



MSP3815

Masterplate® glueable insert rectangular, rectangular with nut



MSP3815

Masterplate® glueable insert rectangular, rectangular with

threaded...



MSP38

Masterplate®
glueable insert Ø38,
Cylindrical Ø38 with
tapped ins...



MSP38

Masterplate®
glueable insert Ø38,
Cylindrical Ø38 with
threaded s...