



Applications

- Motor driven pumps or compressors
- Electrical generators, textile machines
- Iron and steel plants, cement factories.

Determining torque

$$T_{MN} = \frac{N_{kW} \times 9550}{n_{rpm}} = (\text{Nm})$$

Service factor K :

Service	Electric motor	Combustion engine
	steam turbine	hydraulic turbine
Uniform S1	1,0	1,5
Light S2	1,5	2,0
medium S3	2,0	2,5
Heavy S4	2,5	3,0
Very heavy S5	3,0	3,2



Temperature factor St:

St	-20°C	0°C	+20°C	+40°C	+60°C	+70°C	+80°C
	1,0	1,0	1,0	1,0	1,2	1,4	1,6

$$T_{MN} \times K \times St \leq T_{CN} \text{ coupling}$$

$$n \text{ inst.} \leq n_{MAX} \text{ coupling}$$

$$\text{shaft diameter} \leq d_{MAX} \text{ coupling}$$

Safety precautions

The tyre is cut radially to allow mounting/dismounting. Depending on the speed and torque transmitted, an axial force will be generated which must be absorbed by the bearings in the coupled machines. The tyre may expand by up to 5% during use which must be taken into account when choosing a protective housing.

Part number	Nominal torque	Max. torque	Max. speed	Moment of inertia	Misalignment		
	TCN (Nm)	TCmaxi. (Nm)	(rpm)	(kgm ²)	Axial (Nm)	Radial (Nm)	Angular
PNA2-203R	50	150	5 000	0,001	1,0	0,75	2°
PNA6-206R	100	300	5 000	0,003	1,5	1,00	2°
PNA16-210R	200	600	4 000	0,013	2,0	1,30	2°
PNA40-214R	400	1 200	4 000	0,035	2,5	1,60	2°
PNA63-218R	800	2 400	3 000	0,105	3,0	2,10	2°

Dimensions in mm

PERIFLEX® elastic coupling

Torque: 50 to 2400Nm

PNA


- Easy installation, machines to be coupled will not require to be moved
- Backlash free
- Can transmit shocks up to 3 times the value of nominal torque
- Quickly damps vibrations
- Maintenance free

Characteristics

- Large axial misalignment up to 6mm radial up to 5mm angular up to 2°
- Keyway in accordance with NF E22-175/P9 (J59)
- Working temp.: -20°C to +80°C
- Materials:
 - Hub: Steel
 - Locking assembly: Steel
 - Tyre R: Natural rubber (NR) with fabric reinforcements

Options

- Alternative tyre materials (inserts mounted in X pattern)



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number solid coupling	ØA	ØB	ØC	L	M	Ød max.	Ød pre-bore	Ød Standard bores (H7)
PNA2-203R	104	54	40	70	30	28	plein	10, 15, 19, 20, 25, 28
PNA6-206R	136	68	55	110	45	38	plein	10, 15, 20, 25, 30, 35, 38
PNA16-210R	178	88	70	130	50	48	15	20, 25, 30, 35, 38, 48
PNA40-214R ⁽¹⁾	210	116	92	160	65	65	15	20, 25, 30, 35, 40, 45, 50, 55, 60, 65
PNA63-218R ⁽¹⁾	263	140	107	190	75	75	25	30, 35, 40, 45, 50, 55, 60, 65, 70, 75

Part number solid coupling	N	O	P	Number of screws	Screw	Locking torque (Nm)	Weight (kg)	Stock* prebored	Price each full or prebored	Price each bored keyway
PNA2-203R	8	16	66	12	M6	4 ⁽²⁾	1,15	✓	335,76 €	568,57 €
PNA6-206R	8	18	74	16	M6	6 ⁽²⁾	2,50	✓	445,46 €	702,92 €
PNA16-210R	19	35	100	16	M8	15 ⁽²⁾	5,40	✓	564,12 €	823,79 €
PNA40-214R ⁽¹⁾	20	38	99	24	M8	20	9,50	-	821,56 €	1 096,93 €
PNA63-218R ⁽¹⁾	24	44	121	16	M12	25	17,50	-	1 121,57 €	1 464,09 €

*Depending on availability - Dimensions in mm

Our other products



GLP
Small 6 lobe threaded handle - male,
Technopolymer - Steel




PLM-20SC
Threaded cylindrical magnet, With
threaded hole



ACL-PLAngle
Joining plate for aluminium profile,
Angle connection



LINK64
Synchronous AC Motor and- gearbox ,
from 1.3 to 6Nm



AC
Strike for toggle latch,
15mm



TBD
Manual leadscrew table with opposing
threads, 2kg



PR40
Articulated foot Ø50,
Ø 50



E60B
Right angle helical reducers, from 4.50 to
24 Nm



CHM50
Worm and wheel gear reducer, up to 107
Nm



BDPR
Holding arm, Rigid



PR40
Articulated foot Ø50,
Ø 50



PRS100
Stainless steel articulated foot Ø100,
Ø 100

Complementary products



PNA_R
PERIFLEX elastic coupling,
Replacement tyre