



NK17 NW17


Loads up to 50N

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:
 - Slide body: Plastic
 - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6

Small but effective



For M3 screw
DIN 7984 DIN
6912 DIN 84
EN ISO 1707




DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-17-1000	1 Rail (1000mm) + 1 slide	151,7	✓	47,80 €
NW02-17	1 slide only	1,7	✓	4,25 €

*Depending on availability - Dimensions in mm

Our other products



ACLBS
Closing system for aluminium profile, 90° bracket for spherical end...



PRF-GPA
Guide for aluminium profile, Parallel rails



HTD14M_55
HTD Heavy duty timing pulley, HTD14 Cast




MCLred
Reducing sleeve female/female, Cylindrical - steel



PPD
Indexing plunger for sheets, For sheet metal




BABreglable
Adjustable ball pin hardened stainless steel, adjustable



PF30
Worm and wheel gear reducer, up to 8.80 Nm




BOX-SHNA
Hexagonal nut - DIN934, Box set of steel nuts



MR_MMR
Metric section rack, Steel



VB
Small 6 lobe threaded handle - female, Duroplast - Stainless



PO
Pull handle - Multi-sector, Smooth hole



MCL
Cylindrical threaded sleeve, Cylindrical - stainless steel

Complementary products



NSKB
Drylin® Rail end cap, Rail end cap