


## NK17 NW17


Loads up to 50N

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:
  - Slide body: Plastic
  - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6

Small but effective



For M3 screw  
DIN 7984 DIN  
6912 DIN 84  
EN ISO 1707



### DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-17-1000	1 Rail (1000mm) + 1 slide	151,7	✓	47,80 €
NW02-17	1 slide only	1,7	✓	4,25 €

\*Depending on availability - Dimensions in mm

## Our other products



CHMR63  
Worm and wheel gear reducer, up to 196 Nm



SH1  
Parallel axis helical gear, Machined plastic (delrin)



EHD08-3  
Internal epicyclic servo reducers, from 20 to 50 Nm



PTA100ssEB  
Articulated foot with sheet metal base Ø100, Articulated foot



NKX  
Combined bearing without inner ring, Needle and ball bearings




WJUM10  
Drylin® W bearing block, Slide



EHD04  
Internal epicyclic servo reducers, from 3.4 to 7 Nm



SCE\_SS  
Stainless steel U-shaped clamp, Stainless steel



CHM50-MOT  
Asynchronous AC motorgearboxes 0.18 to 0.75kW, 0.18 to



UFX  
Spare tyre UNEFLEX® coupling, range



BAC110  
Swivel storage bin, Storage bin



PP35  
Worm and wheel gear reducer, from 2.20 to 4.10 Nm

## Complementary products



NSKB  
Drylin® Rail end cap, Rail end cap