


- **Levelling foot**
- Non slip base
- **Materials:**
  - Base: Black glass reinforced polyamide (Shore 70)
  - Spindle: Zinc plated steel or stainless 304 (nut not supplied)

### Info.

- Values given for static loads will be reduced in case of a vibrating load



**With non-slip base**



### DISCOUNTS

<b>Qty</b>	1+	20+	50+
<b>Disc.</b>	List -10%	On request	

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Price each	
										<b>Stock*</b>	1 to 19
<b>Steel spindle</b>											
PR105-16-75	103	M16	75	51	20	32	126	129	25000	✓	17,76 €
PR105-16-150	103	M16	150	51	20	32	201	204	25000	✓	21,36 €
PR105-16-225	103	M16	225	51	20	32	276	279	25000	✓	26,31 €
PR105-20-125	103	M20	125	51	20	32	176	179	25000	✓	17,99 €
PR105-20-200	103	M20	200	51	20	32	251	254	25000	✓	21,34 €
PR105-20-250	103	M20	250	51	20	32	301	304	25000	✓	26,31 €
PR105-24-125	103	M24	125	51	20	32	176	179	25000	✓	17,99 €
PR105-24-200	103	M24	200	51	20	32	251	254	25000	✓	21,34 €
PR105-24-250	103	M24	250	51	20	32	301	304	25000	✓	26,31 €
<b>Stainless steel spindle</b>											
PR105-16-75/SS	103	M16	75	51	20	32	126	129	25000	✓	31,56 €
PR105-16-150/SS	103	M16	150	51	20	32	201	204	25000	✓	41,75 €
PR105-16-225/SS	103	M16	225	51	20	32	276	279	25000	✓	53,74 €
PR105-20-125/SS	103	M20	125	51	20	32	176	179	25000	✓	36,50 €
PR105-20-200/SS	103	M20	200	51	20	32	251	254	25000	✓	50,12 €
PR105-20-250/SS	103	M20	250	51	20	32	301	304	25000	✓	58,20 €
PR105-24-125/SS	103	M24	125	51	20	32	175	178	25000	-	36,50 €
PR105-24-200/SS	103	M24	200	51	20	32	250	253	25000	-	50,12 €
PR105-24-250/SS	103	M24	250	51	20	32	300	303	25000	-	58,20 €

\*Depending on availability - Dimensions in mm

## Our other products



SDCcs  
Positioning sleeve for indexing pin, For pin Ø4 to Ø12



FTSN  
Supported shaft for linear guide, Steel shaft / Aluminium support




HTD5M\_15  
HTD Heavy duty timing pulley, HTD5 Aluminium



CNA-CNG  
Right angled mounting plate, Right angled mounting plate for ball jo...



SCR  
Suction cup threaded insert, Adaptor for insert



MF  
Shock Absorber -universal flange, Universal fixing



LRM  
Trapezoidal bronze nut, Bronze - 1 thread



CLM  
Male clevis end, Stainless steel short



H0  
Crossed helical gear crossed axis at 90°, Steel 20NCD2



INS150  
Self tapping insert with collar-coarse thread, With collar-



FAD  
Threaded swivel feet, Swivel feet without anti-slip plate



PRF\_FIX\_ANG  
Fastener for aluminium profile, Angular joint

## Complementary products



PR65C  
Half-articulated foot Ø 65, Ø 65