


- **Levelling foot**
- Non slip base
- **Materials:**
 - Base: Black glass reinforced polyamide (Shore 70)
 - Spindle: Zinc plated steel or stainless 304 (nut not supplied)

Info.

- Values given for static loads will be reduced in case of a vibrating load



With non-slip base



DISCOUNTS

Qty	1+	20+	50+
Disc.	List -10%	On request	

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Price each	
										Stock*	1 to 19
Steel spindle											
PR105-16-75	103	M16	75	51	20	32	126	129	25000	✓	17,76 €
PR105-16-150	103	M16	150	51	20	32	201	204	25000	✓	21,36 €
PR105-16-225	103	M16	225	51	20	32	276	279	25000	✓	26,31 €
PR105-20-125	103	M20	125	51	20	32	176	179	25000	✓	17,99 €
PR105-20-200	103	M20	200	51	20	32	251	254	25000	✓	21,34 €
PR105-20-250	103	M20	250	51	20	32	301	304	25000	✓	26,31 €
PR105-24-125	103	M24	125	51	20	32	176	179	25000	✓	17,99 €
PR105-24-200	103	M24	200	51	20	32	251	254	25000	✓	21,34 €
PR105-24-250	103	M24	250	51	20	32	301	304	25000	✓	26,31 €
Stainless steel spindle											
PR105-16-75/SS	103	M16	75	51	20	32	126	129	25000	✓	31,56 €
PR105-16-150/SS	103	M16	150	51	20	32	201	204	25000	✓	41,75 €
PR105-16-225/SS	103	M16	225	51	20	32	276	279	25000	✓	53,74 €
PR105-20-125/SS	103	M20	125	51	20	32	176	179	25000	✓	36,50 €
PR105-20-200/SS	103	M20	200	51	20	32	251	254	25000	✓	50,12 €
PR105-20-250/SS	103	M20	250	51	20	32	301	304	25000	✓	58,20 €
PR105-24-125/SS	103	M24	125	51	20	32	175	178	25000	-	36,50 €
PR105-24-200/SS	103	M24	200	51	20	32	250	253	25000	-	50,12 €
PR105-24-250/SS	103	M24	250	51	20	32	300	303	25000	-	58,20 €

*Depending on availability - Dimensions in mm

Our other products



BPM-Z
Plastic slotted spring plunger with ball tip, Plastic body + stainless steel tip...



CHAE6555
Decorative screwed hinge, Aluminium



CHT
Asynchronous AC Motor, 0.55 to 1.1kW



ESCON
Speed controller 5A accessories, Kit of 4 cables for DC motor



HFL
One way needle bearing, Needle bearing with flange



PPF
Indexing plunger with flange, with drilled flange



SER69K
Quarter turn latch for the food industry, Stainless steel



VTAP
Magnetic head screw, With rubber coating, With rubber coating



OP2
Mechanical digital position indicator, 3 numbers



DOMI50
Domino 50 adjustable slide, Slide DOMILINE 50



MCL
Cylindrical threaded sleeve, Cylindrical - steel



AT5M AT10M
AT type timing belt per metre, AT5 Steel cored polyurethane

Complementary products



ES
Support base (tripod), Plastic



ES
Bipod support base, Plastic



ES
Simple support base (bipod), Plastic



PR65C
Half-articulated foot Ø 65, Ø 65