



DryLin® N miniature guiding system

Load up to 500N

NK27
NW27

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:
 - Slide body: Zinc
 - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6



NS & NW-01




NS & NW-02

Small but effective


Options

- Rail length up to 3000mm max.


For M4 screw
DIN 7984 / DIN 6912
DIN 84 / EN ISO 1707




Type 1



Type 2



Type 1



Type 2

DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK01-27-1000	1 Rail (1000mm) + 1 slide type 1	300,8	✓	61,50 €
NK02-27-1000	1 Rail (1000mm) + 1 slide type 2	302,5	✓	63,60 €
NW01-27	1 slide type 1 only	10,8	✓	4,78 €
NW02-27	1 slide type 2 only	12,5	✓	6,90 €

*Depending on availability - Dimensions in mm

Our other products



EP7

Electronic digital position indicator, 5 numbers



TFR

Rigid manual tensioner, Fixed



MDPOT

Potentiometer,



ADL_F

Female eye bolt conforms to DIN582, Steel



CHA35

Hinge for aluminium profile, Hinge



EPRC

High helix leadscrew, Cylindrical nut - up to 40mm per rotation




EHD12

Internal epicyclic servo reducers, from 60 to 140 Nm



UGAC_UGET

Connection for threaded actuator rod, Connection for threaded actuat...



PM3

Wormwheel, Machined plastic (delrin)



GPBSS

Threaded spherical knob, Stainless steel 304



PRF-P

Aluminium profile feet support, For feet or casters



DIV_SS

Stainless steel locking bolt, With grip - Stainless steel

Complementary products



NSKB

Drylin® Rail end cap, Rail end cap