



## Load up to 500N

## NK27 NW27

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:
  - Slide body: Zinc
  - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6



NS & NW-01




NS & NW-02

**Small but effective**


### Options

- Rail length up to 3000mm max.


For M4 screw  
DIN 7984 / DIN 6912  
DIN 84 / EN ISO 1707




Type 1



Type 2



Type 1



Type 2 **DISCOUNTS**

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK01-27-1000	1 Rail (1000mm) + 1 slide type 1	300,8	✓	61,50 €
NK02-27-1000	1 Rail (1000mm) + 1 slide type 2	302,5	✓	63,60 €
NW01-27	1 slide type 1 only	10,8	✓	4,78 €
NW02-27	1 slide type 2 only	12,5	✓	6,90 €

\*Depending on availability - Dimensions in mm

## Our other products



TBD

Manual leadscrew table with opposing threads, 40kg



T5P\_T10P

Connecting plate for T type timing belts, T10



CHB

Worm and wheel gear reducer, up to 22 Nm



GAL\_25

Ø25 conveyor roller, Without ball bearing



FF40

Offset spur gear reducer, from 59 to 210 Nm



HK

Manual locking clamp, Manual locking clamp LWL



CM

Tools Hygienic Usit® and Hygienic Design®, Combination spanner



MFB\_MHB

Moulded plastic bevel gear (nylon), 4:1



TCL-ECL

Adjusting nut, Fine thread



PCatherm

Pull handle, Thermoplastic



M

Bellows cover, Accessory:



CAP805

Slat top chain stainless steel, Large range 805

## Complementary products



NSKB

Drylin® Rail end cap, Rail end cap