



DryLin® N miniature guiding system

Load up to 1000N

NK80
NW80

Small but
effective

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:



Slide body: Plastic

Rails: Anodised aluminium

- Symmetrical hole pattern, C5=C6

Options

- Rail length up to 3960mm max.



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-80-1000	1 Rail (1000mm) + 1 slide	1240	✓	106,74 €
NW02-80	1 slide only	100	✓	14,12 €

*Depending on availability - Dimensions in mm

Our other products



SRG

Adjustable latch clamp with strike plate, Stroke from 96mm to 121,7mm



PML

Solid foot mount for heavy loads, Ø 100, 120 or 150



ES

Simple support base (bipod), Plastic




F7-SF-SM

Multifunction display, Right angled mounting bracket



EMS

Stainless steel knurled thumb nut, Knurled




BFD

Locking pin for bush, +180°C



G0

Steel spur gear, Steel 20NCD2



G2

Steel spur gear, Steel 20NCD2



BABFCFO

Ball pin socket, Mounting collar with a



KSTM

Igubal® pillow block bearing, Polymer



PO

Pull handle - Multi-sector, Tapped



CHAsb89

Hinge without pin, Plastic hinge

Complementary products



NSKB

Drylin® Rail end cap, Rail end cap