



DryLin® N miniature guiding system

Load up to 1000N

NK80 NW80

**Small but
effective**

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:



Slide body: Plastic

Rails: Anodised aluminium

- Symmetrical hole pattern, C5=C6

Options

- Rail length up to 3960mm max.



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-80-1000	1 Rail (1000mm) + 1 slide	1240	✓	106,74 €
NW02-80	1 slide only	100	✓	14,12 €

*Depending on availability - Dimensions in mm

Our other products



CHMX_CHMDX

Shaft for worm and wheel reducer CHMR and CHM, CHMR and CHM gearbox...




VEL

Self-gripping cable strip, electric and pneumatic cables



T10_21_AL

T type timing pulley, Economy range - T10 aluminium



PRF-GUM

Aluminium profile anodising polisher, Polishing block



UCP_SS

Stainless steel pillow block bearing, Stainless steel



SCA_SS

Stainless steel flat cable clamp, Stainless steel




PRF-P

Aluminium profile feet support, For feet or casters



WING

Manually tightened wing nut, Stainless steel DIN 314/315



H0

Crossed helical gear crossed axis at 90°, Machined plastic (delrin)



ACLEFS

Floor anchor for aluminium profile, Standard



HK

Manual locking clamp, Manual locking clamp T



CNA-CNG

Right angled mounting plate, Right angled mounting plate for clevis

Complementary products



NSKB

Drylin® Rail end cap, Rail end cap