

Fixable articulated foot Ø40 and Ø50 **Ste****Sta****Stock**

PR40 PR50

Accepts loads up to 11,000N

- Levelling foot
- Rubber anti-slip sole (NBR 70 Shore)
- Black glass fibre reinforced Polyamide base
- Threaded ball ended spindle in plated steel or stainless steel
- Nut not supplied

With non-slip sole

Steel or stainless steel spindle




Advantages

- Self aligning on floor due to use of ball ended rod
- Flexible and non-slip sole

Info.

- If subjected to vibration, the static loads given will be reduced



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Price each 1 to 19
Steel spindle										
PR40-6-25	40	M6	25	27	12	16,5	52	55	5000	- 5,25 €
PR40-6-50	40	M6	50	27	12	16,5	77	80	5000	- 5,25 €
PR40-8-50	40	M8	50	27	12	16,5	77	80	10000	✓ 5,84 €
PR40-8-100	40	M8	100	27	12	16,5	127	130	10000	✓ 8,09 €
PR50-10-75	50	M10	75	30	14	20,0	105	108	11000	✓ 7,88 €
PR50-10-125	50	M10	125	30	14	20,0	155	158	11000	✓ 9,40 €
PR50-12-75	50	M12	75	30	14	20,0	105	108	11000	✓ 8,64 €
PR50-12-125	50	M12	125	30	14	20,0	155	158	11000	✓ 9,65 €
PR50-16-75	50	M16	75	30	16	20,0	105	108	11000	- 9,75 €
PR50-16-125	50	M16	125	30	16	20,0	155	158	11000	- 10,92 €
Stainless steel spindle										
PR40-6-25/SS	40	M6	25	27	12	16,5	52	55	5000	- 7,93 €
PR40-6-50/SS	40	M6	50	27	12	16,5	77	80	5000	- 10,01 €
PR40-8-50/SS	40	M8	50	27	12	16,5	77	80	10000	✓ 10,94 €
PR40-8-100/SS	40	M8	100	27	12	16,5	127	130	10000	✓ 15,60 €
PR50-10-75/SS	50	M10	75	30	14	20,0	105	108	11000	✓ 14,58 €
PR50-10-125/SS	50	M10	125	30	14	20,0	155	158	11000	✓ 17,95 €
PR50-12-75/SS	50	M12	75	30	14	20,0	105	108	11000	✓ 13,43 €
PR50-12-125/SS	50	M12	125	30	14	20,0	155	158	11000	✓ 16,40 €
PR50-16-75/SS	50	M16	75	30	16	20,0	105	108	11000	- 14,87 €
PR50-16-125/SS	50	M16	125	30	16	20,0	155	158	11000	- 17,49 €

*Depending on availability- Dimensions in mm

Our other products



ASH

Hoist ring for welding,
for straight lifts - for
welding



HW_HT

Half-rail guide, Wheel



PTA50

Articulated levelling
foot, pressed base
Ø50, Ø 50



GE

Toggle latches,
Miniature




HTD5M_09

HTD Heavy duty
timing pulley, HTD5
Aluminium



TBE12

Economic mini-table
with trapezoidal
leadscrew, 2kg



GMK17_P

Flat Guide, Flat guide
for conical profile



BCA

Steel splined collar,
Steel



PCS62K

Chain sprocket with
hardened teeth,



WSRM

Cylindrical polymer
nut, Polymer



BLHT30

Right angled gearbox,
from 1.65 to 4.40 Nm



BAGtr

Lead screw clamping
collar, Aluminium

Complementary products



VQT

Quarter-turn clamp
lock, Plastic or
stainless steel button



PR65C

Half-articulated foot Ø
65, Ø 65