

Fixable articulated foot Ø40 and Ø50 **Ste****Sta****Stock**

PR40 PR50

Accepts loads up to 11,000N

- Levelling foot
- Rubber anti-slip sole (NBR 70 Shore)
- Black glass fibre reinforced Polyamide base
- Threaded ball ended spindle in plated steel or stainless steel
- Nut not supplied

With non-slip sole


Steel or stainless steel spindle

Advantages

- Self aligning on floor due to use of ball ended rod
- Flexible and non-slip sole

Info.

- If subjected to vibration, the static loads given will be reduced



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Price each 1 to 19	
Steel spindle											
PR40-6-25	40	M6	25	27	12	16,5	52	55	5000	- 5,25 €	
PR40-6-50	40	M6	50	27	12	16,5	77	80	5000	- 5,25 €	
PR40-8-50	40	M8	50	27	12	16,5	77	80	10000	✓ 5,84 €	
PR40-8-100	40	M8	100	27	12	16,5	127	130	10000	✓ 8,09 €	
PR50-10-75	50	M10	75	30	14	20,0	105	108	11000	✓ 7,88 €	
PR50-10-125	50	M10	125	30	14	20,0	155	158	11000	✓ 9,40 €	
PR50-12-75	50	M12	75	30	14	20,0	105	108	11000	✓ 8,64 €	
PR50-12-125	50	M12	125	30	14	20,0	155	158	11000	✓ 9,65 €	
PR50-16-75	50	M16	75	30	16	20,0	105	108	11000	- 9,75 €	
PR50-16-125	50	M16	125	30	16	20,0	155	158	11000	- 10,92 €	
Stainless steel spindle											
PR40-6-25/SS	40	M6	25	27	12	16,5	52	55	5000	- 7,93 €	
PR40-6-50/SS	40	M6	50	27	12	16,5	77	80	5000	- 10,01 €	
PR40-8-50/SS	40	M8	50	27	12	16,5	77	80	10000	✓ 10,94 €	
PR40-8-100/SS	40	M8	100	27	12	16,5	127	130	10000	✓ 15,60 €	
PR50-10-75/SS	50	M10	75	30	14	20,0	105	108	11000	✓ 14,58 €	
PR50-10-125/SS	50	M10	125	30	14	20,0	155	158	11000	✓ 17,95 €	
PR50-12-75/SS	50	M12	75	30	14	20,0	105	108	11000	✓ 13,43 €	
PR50-12-125/SS	50	M12	125	30	14	20,0	155	158	11000	✓ 16,40 €	
PR50-16-75/SS	50	M16	75	30	16	20,0	105	108	11000	- 14,87 €	
PR50-16-125/SS	50	M16	125	30	16	20,0	155	158	11000	- 17,49 €	


*Depending on availability- Dimensions in mm

Our other products



VCMB

Dual-thread screw
wood/metal, Steel



PRF PSP_PR

Dual purpose strip
and cover for
aluminium profile,
Inserts into slot



LFM

Steel leadscrew,
Medium carbon steel -
1 thread



GLT3-46

Telescopic drawer,



CHA135

Screwed hinge, 135
degrees



SFWR

End support, Surface
mounting



PCS25ECO

Chain sprocket - steel,
6.35mm



VRSSss

Male swivelling lifting
rings stainless steel,
Male swivelling - s...



HTD5M_25

HTD Heavy duty
timing pulley, HTD5



ZDB

Machined plastic
bevel gear , 2:1



PW_PWG05

Wheel - precision
range, Bronze



HLUss

Spoked handwheel,
Stainless steel 316

Complementary products



FAD

Threaded swivel feet,
Swivel feet without
anti-slip plate



PR65C

Half-articulated foot Ø
65, Ø 65



ES

Support base (tripod),
Plastic



ES

Bipod support base,
Plastic