




NK17 NW17


Loads up to 50N

- Linear rail with polymer slide unit
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:
 - Slide unit body: Plastic
 - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6

Small footprint



For M3 screw
DIN 7984 DIN
6912 DIN 84
EN ISO 1707



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-17-1000	1 Rail (1000mm) + 1 slide unit	151,7	✓	54,75 €
NW02-17	1 slide unit only	1,7	✓	5,42 €

*Depending on availability - Dimensions in mm



Loads up to 500N

NK27 NW27

- Linear rail with polymer slide unit
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:
 - Slide unit body: Zinc
 - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6



NS & NW-01




NS & NW-02

Small footprint


Options

- Rail length up to 3000mm max.


For M4 screw
DIN 7984 / DIN 6912
DIN 84 / EN ISO 1707




Type 1



Type 2



Type 1



Type 2

DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK01-27-1000	1 Rail (1000mm) + 1 slide unit type 1	300,8	✓	61,28 €
NK02-27-1000	1 Rail (1000mm) + 1 slide unit type 2	302,5	✓	70,21 €
NW01-27	1 slide unit type 1 only	10,8	✓	6,88 €
NW02-27	1 slide unit type 2 only	12,5	✓	8,27 €

*Depending on availability - Dimensions in mm





NK40 NW40


Loads up to 700N

- Linear rail with polymer slide unit
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur[®] J
- Materials:
 - Slide unit body: Zinc
 - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6

Small footprint



For M4 screw
DIN 7984 DIN
6912 DIN 84
EN ISO 1707
EN ISO 7045



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-40-1000	1 Rail (1000mm) + 1 slide unit	480	✓	88,29 €
NW02-40	1 slide unit only	30	✓	13,62 €

*Depending on availability - Dimensions in mm



DryLin[®]N miniature guiding system

Loads up to 1000N

NK80 NW80


- Linear rail with polymer slide unit
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur[®] J
- Materials:
 - Slide unit body: Plastic
 - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6

Small footprint



Options

- Rail length up to 3960mm max.



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-80-1000	1 Rail (1000mm) + 1 slide unit	1240	✓	114,66 €
NW02-80	1 slide unit only	100	✓	19,60 €

*Depending on availability - Dimensions in mm