



DryLin® N miniature guiding system

Load up to 1000N

NK80
NW80

Small but
effective

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:



Slide body: Plastic

Rails: Anodised aluminium

- Symmetrical hole pattern, C5=C6

Options

- Rail length up to 3960mm max.




DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-80-1000	1 Rail (1000mm) + 1 slide	1240	✓	106,74 €
NW02-80	1 slide only	100	✓	14,12 €

*Depending on availability - Dimensions in mm

Our other products




TBL
Mini leadscrew table
with metric thread,
1kg




H4
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



PAL
Self locking counter
nut, For axial locking



RPP8
RPP heavy duty
timing belt, RPP8




CFC
Spring loaded position
switch, Electric
contact



PRF_PGN
Door handle for
aluminium profile,
Handle with lock
suitable



SA_SAKH
Housing for linear
bearing, Closed - light
load



PF45
Worm and wheel gear
reducer, up to 40 Nm



CAP821
Slat top chain acetal,
Large range 821



SER69K-CLE
Quarter turn latch for
the food industry,
Stainless steel key



PGNT
Thermoplastic T
handle, With threaded
insert



BTC_M
End cap with threaded
insert for square tube,
With threaded insert

Complementary products



NSKB
Drylin® Rail end cap,
Rail end cap