



# Idler sprocket for plate chain

For chain ranges 820 and 815

PR820

- For use with CAP820 and CAP815 plate chains

- Materials:

Reinforced polyamide

Stainless steel screws


- Operating temp.: -10°C to +120°C

- For dimensions and bore tolerances, please refer to technical pages


## Advantage

- Two part design facilitates easy assembly

Easy assembly



Two part design




## DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR820-21-25	21	129	129,26	25	0,4	30,67 €
PR820-21-30	21	129	129,26	30	0,4	30,67 €
PR820-21-35	21	129	129,26	35	0,4	30,67 €
PR820-21-40	21	129	129,26	40	0,4	30,67 €
PR820-21-45	21	129	129,26	45	0,4	30,67 €
PR820-23-25	23	141	141,22	25	0,5	32,38 €
PR820-23-30	23	141	141,22	30	0,5	32,38 €
PR820-23-35	23	141	141,22	35	0,5	32,38 €
PR820-23-40	23	141	141,22	40	0,5	32,38 €
PR820-23-45	23	141	141,22	45	0,5	32,38 €
PR820-25-25	25	153	153,20	25	0,5	32,71 €
PR820-25-30	25	153	153,20	30	0,5	32,71 €
PR820-25-35	25	153	153,20	35	0,5	32,71 €
PR820-25-40	25	153	153,20	40	0,5	32,71 €
PR820-25-45	25	153	153,20	45	0,5	32,71 €

Dimensions in mm

## Our other products



QNJ

Single row cylindrical roller bearing, Single flange on inner ring



PM2

Worm and wheel set, Bronze



LR

Precision locknut, Precision locknut



VPPTss

Stainless steel handwheel with handle, Stainless steel 304




SLBE

Indexing plunger - Spacer, Spacer for SLB and SLBS index bolts



T10\_21\_AL

T type timing pulley, Economy range - T10 aluminium



AC

Strike for toggle latch, 18mm



DIA

Ring operated locking bolt, with ring



GB-RA

Brass spur gear, Brass CuZn39Pb3



HLC24

Right angle spiro bevel gearbox, Up to



PSG15

Spur gear - precision range, Stainless steel



AF

Shaft clamp with keyway, Set screw

## Complementary products



CAP820

Slim slat top chain acetal, Narrow straight range 820



CAP815

Slim slat top chain stainless steel, Narrow range 815



DBL820

Idler for slat top chain, Ranges 820 and 815



PT820

Drive sprocket for slat top chain, Ranges 820 and 815