

Digital position indicator

Size XS Stock

OP3DX
OP3SX

4 digit display

Stainless steel version available on request


- 4 digit display (9999) with red digits for tenths/hundredths
- Shaft driven position indicator
- Displays linear or angular movement by use of mechanism driven by a rotating shaft
- Nonflammable polycarbonate case Protection IP64
- Max. temperature 80°C
- Colour: orange
- Height of digits: 5mm
- Standard bore for shaft 14H7, smaller bores will require use of reducing sleeve



Gasket supplied



Clamp spacer OP3-BE




Options

- Version with stainless steel parts available
- Anti-rotation pin Ø6mm





Assembly

- Insert the indicator on to the shaft ensuring that the torque pin is inserted into the 5mm hole that should have been provided. Reset the display to zero and secure the fixing screw.

Shaft hole max. Ø14



OP3DX OP3SX



DISCOUNTS

Qty	1+	5+	+10
Disc.	List	-15%	On request

Part number	View	Pitch (mm)	Display after one turn (mm)	Max. speed (rpm)	Counting direction	Stock*	Price each 1 to 4
OP3-A10-DX	A	1	001 0	300	clockwise	✓	66,11 €
OP3-A20-DX	A	2	002 0	300	clockwise	✓	66,11 €
OP3-A40-DX	A	4	004 0	250	clockwise	✓	66,11 €
OP3-A50-DX	A	5	005 0	200	clockwise	✓	66,11 €
OP3-A100-DX	A	10	010 0	150	clockwise	✓	66,11 €
OP3-B10-DX	B	1	001 0	300	clockwise	✓	66,11 €
OP3-B20-DX	B	2	002 0	300	clockwise	✓	66,11 €
OP3-B40-DX	B	4	004 0	250	clockwise	✓	66,11 €
OP3-B50-DX	B	5	005 0	200	clockwise	-	66,11 €
OP3-B100-DX	B	10	010 0	150	clockwise	-	66,11 €
OP3-A10-SX	A	1	001 0	300	anticlockwise	✓	66,11 €
OP3-A20-SX	A	2	002 0	300	anticlockwise	-	66,11 €
OP3-A40-SX	A	4	004 0	250	anticlockwise	✓	66,11 €
OP3-A50-SX	A	5	005 0	200	anticlockwise	-	66,11 €
OP3-A100-SX	A	10	010 0	150	anticlockwise	✓	66,11 €
OP3-B10-SX	B	1	001 0	300	anticlockwise	-	66,11 €
OP3-B20-SX	B	2	002 0	300	anticlockwise	-	66,11 €
OP3-B40-SX	B	4	004 0	250	anticlockwise	-	66,11 €
OP3-B50-SX	B	5	005 0	200	anticlockwise	-	66,11 €
OP3-B100-SX	B	10	010 0	150	anticlockwise	-	66,11 €

*Depending on availability - Dimensions in mm

Our other products



RBG

Wheel, Grey rubber -
Polypropylene rim



VTAP

Magnetic head screw,
With rubber coating
With rubber coating



PCS5055

Chain sprocket -
Stainless steel,
12.7mm (DIN 08B-1)



CHA_GC_955

Stainless steel garnet
hinge, To be welded



PTA80ssEB

Articulated foot with
sheet metal base
Ø80, Articulated foot



DB

Steel bevel gear, 2:1



PTAF80-PAMF80

Articulated fixable
foot with pressed
base Ø80, Ø 80



ACLALF

Adjustable foot for
aluminium profile,
Ideal for workstations



PRF_GAL

Roller for aluminium
profile, Hollow roller
Ø12



DKN

Bellows coupling
Gerwah®, from 0.4 to
10Nm



PO

Pull handle - Multi-
sector, Tapped
recessed insert



LRX

Linear roller slide, Rail
- from 9410 N to
101000 N

Complementary products



OP3_14_06

Reducing sleeve for
OP indicators,
Reduction socket



OPFL_OPMP

Numerical counter
accessories, Locking
clamp



LFM

Steel leadscrew,
Medium carbon steel -
1 thread



VPRA_M

Handwheel with
handle,
Thermo-setting plastic
- galvanised steel hub